

ASTRA-LAV™ VANITY TOP

Made In U.S.A.



- One piece, seamless vanity top
- 3/4" thick deck
- High quality cultured marble with extra thick wear layer
- Recessed oval bowl design
- Raised faucet deck and no-drip edge
- 4" back splash
- 4" faucet centers
- Less faucet, drain assembly and supply
- Custom sizes available

- CMA8197**
- CMA8259**
- CMA8319**
- CMA8379**
- CMA8499**
- CMA8619**
- CMA8619** Double Bowl

Bowl sizes:

15" (381mm) wide
10" (254mm) front to back
4-3/4" (121mm) deep

- CMA8254**
- CMA8314**
- CMA8374**
- CMA8434**
- CMA8494**
- CMA8614**
- CMA8612** Double Bowl
- CMA8734** Double Bowl

Bowl sizes:

15" (381mm) wide
12" (305mm) front to back
5-1/4" (133mm) deep

Compliance Certifications -

Meets or Exceeds the Following Specifications:

- CSA B45.5
- IAPMO Z 124




To Be Specified

- Color:
- Faucet:
- Faucet Finish:
- Supplies:
- Trap:


* See faucet section for additional models available

SEE REVERSE FOR PRODUCT DIMENSIONS
AND SPECIFICATIONS



MODEL #	SIZE
CMA8197	19" x 17"
CMA8259	25" x 19"
CMA8319	31" x 19"
CMA8379	37" x 19"
CMA8499	49" x 19"
CMA8254	25" x 22"
CMA8314	31" x 22"
CMA8374	37" x 22"
CMA8434	43" x 22"
CMA8494	49" x 22"

DIMENSIONS									
MODEL #	DIM A	DIM B	DIM C	DIM D	DIM E	NOMINAL BOWL SIZE	NOMINAL BOWL DEPTH		
CMA8197	19"	17"	9"	3"	6-1/4"	15" x 10"	4-3/4"		
CMA8259	25"	19"	9"	3"	6-1/2"	15" x 10"	4-3/4"		
CMA8319	31"	19"	9"	3"	6-1/2"	15" x 10"	4-3/4"		
CMA8379	37"	19"	9"	3"	6-1/2"	15" x 10"	4-3/4"		
CMA8499	49"	19"	9"	3"	6-1/2"	15" x 10"	4-3/4"		
CMA8254	25"	22"	9"	3"	7-1/4"	15" x 12"	5-1/4"		
CMA8314	31"	22"	9"	3"	7-1/4"	15" x 12"	5-1/4"		
CMA8374	37"	22"	9"	3"	7-1/4"	15" x 12"	5-1/4"		
CMA8434	43"	22"	9"	3"	7-1/4"	15" x 12"	5-1/4"		
CMA8494	49"	22"	9"	3"	7-1/4"	15" x 12"	5-1/4"		



MODEL #	SIZE
CMA8619	61" x 19"
CMA8619 - Double Bowl	61" x 19"
CMA8614	61" x 22"
CMA8612 - Double Bowl	61" x 22"
CMA8734 - Double Bowl	73" x 22"

DIMENSIONS									
MODEL #	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F	DIM G	NOMINAL BOWL SIZE	NOMINAL BOWL DEPTH
CMA8619	61"	19"	9"	3"	6-1/2"	N/A	30-1/2"	15" x 10"	4-3/4"
CMA8619	61"	19"	9"	3"	6-1/2"	15-1/2"	N/A	15" x 10"	4-3/4"
CMA8614	61"	22"	9"	3"	7-1/4"	N/A	30-1/2"	15" x 12"	5-1/4"
CMA8612	61"	22"	9"	3"	7-1/4"	15-1/2"	N/A	15" x 12"	5-1/4"
CMA8734	73"	22"	9"	3"	7-1/4"	15-1/2"	N/A	15" x 12"	5-1/4"

NOTES:
* DIMENSIONS SHOWN FOR LOCATION OF SUPPLIES AND "P" TRAP ARE SUGGESTED.
FITTINGS NOT INCLUDED WITH FIXTURE AND MUST BE ORDERED SEPARATELY.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.9M. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.