

# Miller DuraFlex® Python ULTRA

## P950QC Series



### Description

DuraFlex Python® ULTRA, available in green or blue, is a stretchable full-body harness with friction buckle shoulder straps, quick connect leg buckles, quick connect chest strap buckle, sliding back D-ring, sub-pelvic strap, tool belt loops, Comfort-touch back D-ring pad and pull-free lanyard rings.

### Materials

<b>Webbing (DuraFlex)</b>	Polyester, Urethane Elastomer
<b>Webbing</b>	1-3/4" Dacron polyester
<b>Minimum Tensile Thread</b>	5000 lbs. on webbing 6 cord bonded 3 strand polyester thread. Minimum tensile of 42 lbs.
<b>Grommet</b>	Brass
<b>Hardware</b>	Steel
<b>D-Rings</b>	5000 lbs. (22kN)
<b>Buckles</b>	4000 lbs. (18kN)
<b>Label Materials</b>	Lexan and Valeron
<b>Label Contents</b>	Bar Coding, Inspection, Type, Model, Date, Serial No., Material Specs, Size, Capacity, Certifications.

\* All hardware meets ASTM (50) fifty-hour salt spray test requirements.

### Technical

<b>Max. Working Load</b>	400lbs (181.4kg)
<b>Webbing Min.Tensile</b>	5000lbs (22kN)
<b>D-ring Min. Tensile</b>	5000lbs (22kN)
<b>Buckle Min. Tensile</b>	4000lbs (18kN)

### Certification

Meets or exceeds all OSHA, ANSI, and CSA specifications.

Also available in blue polyester webbing for greater chemical resistance. (Model P950DQC/UBL)



**P950QC  
Shown**



*Additional Features are indicated within the harness Catalog Number.*

Model No.	Web Type	D-Rings	Shoulder Straps	Leg Straps	Chest Strap	Special Features	Weight
<b>P950QC</b>	DP	B	FB	QC	QC	SP, LR	3.15 lbs. (1.4 kg)
<b>P950QC-7</b>	DP	B, S	FB	QC	QC	SP, LR	3.75 lbs. (1.7 kg)
<b>P950QC-77</b>	DP	B, S	FB	QC	QC	BL,SP,LR,BP,RB	5.60 lbs. (2.5 kg)
<b>P950DQC</b>	DDP	B	FB	QC	QC	SP,LR	3.15 lbs. (1.4 kg)
<b>P950DQC-7</b>	DDP	B, S	FB	QC	QC	SP, LR	3.75 lbs. (1.7 kg)
<b>P950DQC-77</b>	DDP	B, S	FB	QC	QC	BL,SP,LR,BP,RB	5.60 lbs. (2.5 kg)

*Refer to next page for harness description keys.*

# Miller DuraFlex<sup>®</sup> Python ULTRA

## P950QC Series

### **Shoulder/Leg Buckles**

FB = Friction Buckles

MB = Mating Buckles

TB = Tongue Buckles

### **D-Rings**

B = Sliding Back D-Ring

FD = Front D-Ring

F = Front O-Ring

H = Shoulder D-Rings

S = Side Positioning D-Rings

W = Sliding Back web D-Ring

X = D-Ring Web Extension

### **Webbing**

D = DuraFlex Stretchable Webbing

DP = DuraFlex Python Webbing

DDP = Dacron Python Webbing

K = Kevlar Webbing

N = Nylon Webbing

P = Polyester Webbing

### **Special Features**

AB = Attached Waist Belt

AL = Adjustable Belt Loops

BL = Belt Loops

BP = Back Pad

HP = Shoulder Pads

LP = Leg Pads

LR = Lanyard Ring

RB = Removable Waist Belt

SP = Sub-Pelvic Strap

SR = Self Rescue Loops

SS = Saddle Seat

TO = Tool Belt Buckles



by Honeywell

Toll Free 800.873.5242 (press 4) • [hsptechsupport@honeywell.com](mailto:hsptechsupport@honeywell.com) • [www.millerfallprotection.com](http://www.millerfallprotection.com)

**⚠ WARNING!** THIS DOCUMENT PROVIDES AN OVERVIEW OF FALL PROTECTION PRODUCTS AVAILABLE FROM HONEYWELL AND CARE HAS BEEN TAKEN TO ASSURE THE ACCURACY OF THE DATA. IT DOES NOT PROVIDE IMPORTANT PRODUCT WARNINGS AND INSTRUCTIONS. HONEYWELL RECOMMENDS ALL USERS OF FALL PROTECTION EQUIPMENT UNDERGO THOROUGH TRAINING, AND THAT ALL WARNINGS AND INSTRUCTIONS PROVIDED WITH THE PRODUCTS BE THOROUGHLY READ AND UNDERSTOOD PRIOR TO EACH USE. FAILURE TO READ AND FOLLOW ALL PRODUCT WARNINGS AND INSTRUCTIONS COULD RESULT IN SERIOUS INJURY OR DEATH.