


Type _____

-104

P4675 ☐

Catalog No.	Finish	Lamping	Dimensions (Inches)		
	Polished Nickel		A	B	C
P4675	-104	9 (c) (G16.5) 60w	31	15-3/8	82



Specifications:

General

- Opal etched glass drum shades: 5-7/8" dia., 3-3/8" ht.
- Plated Polished Nickel (-104) finish
- Steel construction
- One 6", four 12" lengths of stem included
- 6 Links of 9 gauge chain included
- Companion fixtures are available

Mounting

- Ceiling stem mounted with 6 links of chain mount
- Canopy covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included
- Threaded socket ring secures glass

Electrical

- Candelabra base ceramic sockets
- 15 feet of wire supplied
- Pre-wired

Labeling

- UL-CUL Dry location listed