


Type _____

-104WB

P2920 ☐

P2927 ☐

| Catalog No. | Finish | Lamping | Dimensions (Inches) | | | |
|-------------|-----------------|--------------------------------|---------------------|-------|-------|---|
| | Polished Nickel | | A | B | C | D |
| P2920 | -104WB | 2 (c) (Krypton) 60w (included) | 15 | 7-3/8 | 7-7/8 | 4 |
| P2927 | -104WB | 3 (c) (Krypton) 60w (included) | 22-7/8 | 7-3/8 | 7-7/8 | 4 |



Specifications:

General

- Opal etched drum shades: 5-7/8" dia., 3-3/8" ht.
- Plated Polished Nickel finish
- Steel construction
- Threaded socket ring secures glass
- Companion Bath and Vanity, Chandelier, Pendant, Sconce, fixtures are available

Mounting

- Wall mount
- Back plate covers a standard 4" hexagonal recessed outlet box: 11-7/8" W., 4-5/8" ht.
- Mounting strap for outlet box included

Electrical

- Candelabra base sockets
- Pre-wired

Labeling

- UL-CUL Damp location listed