





## **Standard Features & Accessories**

#### All models include

- Capacity—1.0 cu. ft.
  o 17-11/32"W. x 5-7/8"H. x 17-1/8"D.
- Commercial type-styling and design
- Digital LCD display
- 11 Sensor settings
- Sensor popcorn/sensor reheat
- Automatic defrost
- Add-a-minute allows you to add a minute to cooking time by simply touching a button
- Warm/hold feature allows you to keep food warm for up to 30 minutes
- Child lock safety feature locks the control panel to prevent unwanted operation
- Timer function
- Place undercounter below cooktop, rangetop, or as stand-alone unit

## **Model Options**



VMOD240 Professional



DMOD240 Designer

FINISH DETAILS FOR ALL MODELSStainless Steel (SS)








# **Dimensions & Specifications**


PRODUCT DIMENSIONS & DRAWER EXTENSION



	VMOD240	DMOD240	
Overall width	23-7/8" (60.6 cm)		
Overall height (from bottom)	15-5/8″ (39.7 cm)		
Overall depth (from rear)	25-1/8 (63.8 cm)		
Interior			
Width	17-11/32" (44.1 cm)		
Height	5-7/8" (14.	.9 cm)	
Depth	17-1/8" (43.5 cm)		
Approx. ship weight	103 lb. (46.7 kg)		







	All models	
Cutout width	22-1/8" (56.2 cm)	
Cutout height	14-13/16" (35.1 cm)	
Cutout depth	23-1/2" (59.7 cm) min.	



PLANNING AND DESIGN GUIDE VIKINGRANGE.COM • 1-888-VIKING1



## COOKING Undercounter DrawerMicro™ Oven



Compliance Information  $(\underline{\Psi}_{L})_{c}(\underline{\Psi}_{L})$ 

### WARRANTY INFORMATION\*

- Three-year full covers complete unit (Professional Series)
- One-year full warranty—complete product (Designer Series)
- Five-year limited magnetron tube (Professional and Designer)
- Ninety-day limited cosmetic parts such as glass, painted items, and decorative items (Professional and Designer)
- \* For complete warranty see Use & Care Guide. Warranty valid on Viking products shipped within the United States and Canada.

(VIKING)

PLANNING AND DESIGN GUIDE VIKINGRANGE.COM • 1-888-VIKING1