



CLEAN CLOTHES, CLEAN CONSCIENCE

Our commitment to bringing affordable and efficient appliances to our customers is reflected in the resource-saving features of our high-efficiency top load pair.* Now you can use less water to get the same great clean, while also conserving energy. In addition, many of our other top load pairs offer large capacity and multiple cycles and options, so you always have the right space and settings for the load.

*Refers to NTW4750Y and NE/GD4700Y models only.

Amana®

HIGH EFFICIENCY ALL AROUND

Our HE top load washer exceeds government standards for ENERGY STAR® qualification and meets CEE Tier 3* standards, helping you conserve resources and lower utility bills.



WASH AND DRY MORE AT ONCE


Our biggest capacity top load laundry pair fits more in every load. Now you can conserve resources and cut down on the time and energy spent doing laundry.

HIGH EFFICIENCY IN A TOP LOAD FORMAT

OUR HE WASHER USES UP TO 75% LESS WATER
AND 82% LESS ENERGY,** HELPING YOU SAVE OVER \$1,200
IN UTILITY COSTS OVER ITS LIFETIME.†

SENSES WHEN ITEMS ARE DRY

Automatic Dryness Control uses a sensor to monitor air temperature, automatically stopping the cycle when fabrics are dry to help reduce shrinking and overdrying.



CLEAN WITH LESS WATER

A low-water wash system cleans efficiently with as little as 13 gallons of water. Rather than filling the basket, a concentrated detergent and water mix penetrates fabrics to help remove soils and stains.

Note: Not all features included on all models. *Based on the Consortium for Energy Efficiency qualifying product list. Visit cee1.org for more information.
**Compared to pre-2004 traditional top load washers. †Compared to pre-2004 traditional top load washers, average use, normal cycle, 10-year life.

MODEL LINEUP

WASHERS



3.4
CU.FT.

NTW4600Y



3.4
CU.FT.

NTW4650Y*



3.4
CU.FT.

NTW4700Y



3.6
CU.FT.

NTW4750Y*

DRYERS



6.5
CU.FT.

NE/GD4600Y



7.0
CU.FT.

NE/GD4700Y



*For every Amana® major appliance sold, a tree will be planted to help rebuild global deforested areas.***

*Indicates a retail-specific model

**During 2013, for every major appliance it sells in the U.S., Amana® will donate \$0.10 (the cost of each tree planted). Total donation is expected to plant over 2 million trees.

SPECIFICATIONS

TOP LOAD WASHERS	NTW4600Y	NTW4650Y*	NTW4700Y	NTW4750Y*
Capacity (cu. ft.)	3.4	3.4	3.4	3.6
ENERGY STAR® qualified				•
High efficiency				•
Spin speed (RPM)	Up to 700	Up to 700	Up to 700	up to 800
Number of cycles	9	9	11	12
Clean Washer with affresh® Washer Cleaner				•
Quick Wash				•
Super Wash				•
Hand Wash		•	•	
Soak				•
Bulky				•
Casual Heavy	•	•	•	•
Casual Light	•		•	
Casual Regular	•	•	•	
Heavy	•	•	•	•
Light	•	•	•	•
Regular	•	•	•	•
Delicates	•	•	• Regular and Light	•
Drain & Spin	•	•	•	•
Rinse & Spin	•	•	•	•
Extra Rinse option				•
Auto load sensing				•
Stain Treat option				•
Cycle status bar	•	•	•	•
Water levels	3	3	3	Auto
Water temperatures	3	3	4	5
Custom options	6	6	10	11
Dispensers	Bleach	Bleach	Bleach and fabric softener	Bleach and fabric softener
Washer lid opening	Standard	Standard	Wide	Wide
Wash basket	Spreckle, porcelain	Spreckle, porcelain	White, porcelain	Stainless Steel
Wash system	Agitator	Agitator	Dual action agitator	Low water, impeller
Color	Q	Q	Q	Q

DRYERS	NE/GD4600Y	NE/GD4700Y
Capacity (cu. ft.)	6.5	7.0
Number of cycles	11	12
Heavy Duty		•
Timed Dry	up to 60 min.	up to 70 min.
On/off end-of-cycle signal		•
Temperature settings	3	4
Automatic Dryness Control	•	•
Energy Preferred	•	•
Wrinkle Prevent option	•	•
Interior drum light		•
Reversible-swing door	Wide-open, side-swing	Wide-open, side-swing
Optional drying rack	3404351	3406839
LP conversion kit (gas models only)	49572A	49572A
Color	Q	Q

Bold green type indicates a step-up feature

Q White


DIMENSIONS

TOP LOAD WASHERS

MODEL	Height to top of console (A)	Height to top of cabinet (B)	Width (C)	Depth (D)	Height with lid opened 90° (E)
NTW4600Y	43"	37"	25½"	26"	53"
NTW4650Y*	43"	37"	25½"	26"	53"
NTW4700Y	43"	37"	25½"	26"	53"
NTW4750Y	43"	37"	25½"	26"	53"

DRYERS

MODEL	Height to top of console (A)	Height to top of cabinet (B)	Width (C)	Depth (D)	Depth with door opened 90° (E)
NE/GD4600Y	43"	37"	29"	28½"	50½"
NE/GD4700Y	43"	37"	29"	28½"	50½"



*Indicates a retail-specific model.

DIMENSIONS ARE SHOWN FOR PLANNING PURPOSES ONLY. For complete information, see Installation Instructions packed with product.