

٠.	Todact opecinications for E22000 1201 0				
	Job Name:	Job Type:			
	oo rume.	100 1)pc.			
	Quantity:	Comments			



E22380-120PC **Veil 5-Light Flush Mount** 

**Finish** Polished Chrome

Lamping

Number of Bulb(s)	5
Light Type	Xenon
Bulb Type	G9
Max Bulb Wattage	50
Max Fixture Wattage	250
Rated Life	±2,000 Hours
Rated Lumens	±4,000
Color Temp	±2,900 K
Bulb(s) Included	Yes
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	No
Dimmable	Standard

# Glass/Shade

Other

**UPC Code** 

Material

Measurements

#### Width 15.00" Height 13.75" Length Extension **Back Plate Width**

Back Plate Height	N/A
НСО	N/A
Min Overall Height	N/A
Max Overall Height	N/A
Hanging Weight	7.16 lb(s)
Height Adjustable	N/A
Slope	N/A
Chain Length	N/A
Wire Length	N/A
Canopy Width	N/A
Canopy Height	N/A
Canopy Length	N/A

# **Product Category**

### Flush Mount

N/A

N/A

N/A

Shipping	
Carton Weight	10.76 lb(s)
Carton Width	17.00"
Carton Height	13.50"
Carton Length	17.00"
Carton Cubic Feet	N/A
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

## Certification

Safety Rating	Dry
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No

# **Equivalents**

845094050544	Incandescent Watts	
N/A	Fluorescent Watts	N/A

ET2 Contemporary Lighting and all designs, logos and images © 2015 ET2 Contemporary Lighting. All Rights Reserved. ET2 Contemporary Lighting reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes. Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.