

# S2419 A19

## Incandescent

60A19/CL/120V VINTAGE

Lamp Type	Incandescent
Bulb Type	A19
Base Type	E26
Wattage	60



### Lighting Facts Per Bulb

**Brightness** 240 lumens


**Estimated Energy Cost** \$7.23

per year, based on 3 hrs/day, 11c/kWh.  
Energy cost depends on utility rates and light use.

**Average Life** 2.7 years

Based on 3 hrs/day

### Light Appearance



**Energy Used** 60 watts

## Product Information

### Features

- Vintage Style incandescent
- Historic restoration quality
- Classic, warm glow

## Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S2419	Incandescent	*20045923024195	120	60	n/a	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	60A19/CL/120V/Vintage	Yes	n/a	4 1/2	2 3/8	240	3000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
n/a	n/a	n/a	n/a	48	Box	n/a	Yes