

## **22100 SERIES**

# **SMALL SUMP, Combination Drain/Overflow**

#### **APPLICATION**

Used on small roofs, gutters or valleys of any construction. Integral outlets for roof and overflow drainage in one-piece body for limited space installation. WEJLOC® compression flashing clamps hold the membrane or flashing to the drain body. Small beehive domes provide ample drainage for small roof decks and intercept debris.

#### **SPECIFICATION**

JOSAM 22100 Series coated cast iron combination Roof Drain and Overflow Drain with cast iron domes, two WEJLOC® non-puncturing clamp rings with integral gravel stops, integral cast iron standpipe in cast iron deck flange and dual no-hub bottom outlets.

# **Available Options**


- -10 Fixed Extension Collar, Cast Iron, (Specify Hgt) 1" Std.
- -20 Galvanized Cast Iron Parts
- -23 Rough Bronze Dome
- -28 Cast Iron Dome for Overflow Drain
- -33 Stainless Mesh Screen-Covered Dome

-VP Vandal-Proof Dome

-IRMA Perforated Stainless Steel

#### OUTLETS:

-Z No-Hub Spigot Outlets



FOR OUTLET TYPE SPECIFY -Z						
TYPE NO.	PIPE SIZE	LBS.				
22102	2	37				
22103	3	37				
22104	4	38				

## **22200 SERIES**

# **MEDIUM SUMP, Combination Drain/Overflow**

#### **APPLICATION**

Combination Roof Drain/Overflow Drain. One-piece double drain receiver positions roof drain, overflow drain side by side, requiring single deck penetration. Medium sumps selected for anticipated flow. Combination non-puncturing clamp ring, gravel stop ensures watertight seal at the surface.

### **SPECIFICATION**

JOSAM 22200 Series coated cast iron 12" diameter Combination Roof Drain and Overflow Drain, one WEJLOC® non-puncturing clamp ring with integral gravel stop and cast iron dome, one non-puncturing clamp ring with solid waterguard, double drain receiver and clips and cast iron beehive dome.


# **Available Options**

- Fixed Extension Collar, Cast Iron, (Specify Hgt) 1" Std.
- -20 Galvanized Cast Iron Parts
- -23 Rough Bronze Domes
- -33 Stainless Mesh Screen-Covered Domes
- -VP Vandal-Proof Domes

-IRMA Perforated Stainless Steel Extensions

#### **OUTLETS:**

- -T Threaded Outlets
- -X Inside Caulk Outlets
- -Z No-Hub Spigot Outlets



\* 5-5/8" DIM. (BODY HGT.) VARIES BY OUTLET SIZE WITH -T AND -X CONNECTIONS.

FOR OUTLET TYPE SPECIFY -1, -X or -Z								
TYPE NO.	PIPE SIZE	LBS.	TYPE NO.	PIPE SIZE	LBS.			
22202	2	55	22205	5	55			
22203	3	55	22206	6	55			
22204	4	55						

# **22500 SERIES**

# **LARGE SUMP, Combination Drain/Overflow**

### **APPLICATION**

Combination Roof Drain/Overflow Drain. One-piece double drain receiver positions roof drain, overflow drain side by side, requiring single deck penetration. Large sumps selected for anticipated flow. Combination non-puncturing clamp ring, gravel stop ensure watertight seal at the surface.

#### **SPECIFICATION**

JOSAM 22500 Series coated cast iron 15" diameter Combination Roof Drain and Overflow Drain, one WEJLOC® non-puncturing clamp ring with integral gravel stop, one WEJLOC® non-puncturing clamp ring with internal waterguard, double drain receiver and clips and two large polypropylene locking domes.

# **Available Options**


- -10 Fixed Extension Collar, Cast Iron, (Specify Hgt) 4" Std.
- -20 Galvanized Cast Iron Parts
- -23 Rough Bronze Domes
- -28 Cast Iron Dome for Overflow Drains
- -33 Stainless Mesh Screen-Covered Domes

-VP Vandal-Proof Domes

-IRMA Perforated Stainless Steel

#### OUTLETS:

- JTLETS:
  -T Threaded Outlets
- -X Inside Caulk Outlets
- -Y Hub Outlets w/Gasket, 2"-4"
- -Z No-Hub Spigot Outlets



FOR OUTLET TYPE SPECIFY -T, -X, -Y or -Z							
TYPE NO.	PIPE SIZE	LBS.	TYPE NO.	PIPE SIZE	LBS.		
22502	2	65	22506	6	65		
22503	3	65	22508	8	65		
22504	4	65	22509-Z	10†	65		
22505	5	65	† 10" AVAILABLE IN NO-HUB ONLY				