

**PFXC SERIES**

# Corrugated Water Heater Connectors



### Product Features

- Stainless steel corrugated
- Kink resistant
- IAPMO listed
- NSF 61 compliant
- AB 1953 Compliant
- ASME A112.18.6
- Max pressure: 125 psi
- Working Temperature : 40°F - 160°F
- Max. Temperature: 180°F



**PFXCHF18**

MODEL NUMBER	DESCRIPTION	LENGTH (IN)	LENGTH (MM)
PFXCHF18	LF 3/4 FIPXPUSH 18 SS COR WHTR CONN	18"	457.2mm
PFXCHFT18	LF 3/4 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHFT24	LF 3/4 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHGT18	LF 1 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHGT24	LF 1 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHHT18	LF 1-1/4 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHJT18	LF 1-1/2 FIP 18 SS COR WHTR CONN	18"	457.2mm
PFXCHGFT24	LF 1X3/4 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHHGT24	LF 1-1/4X1 FIP 24 SS COR WHTR CONN	24"	609.6mm
PFXCHFM18	LF 3/4 MXF 18 SS COR WHTR CONN	18"	457.2mm
PFXCHFM24	LF 3/4 MXF 24 SS COR WHTR CONN	24"	609.6mm
PFXCHF18	LF 3/4 FIPXSWT 18 SS COR WHTR CONN	18"	457.2mm
PFXCHF24	LF 3/4 FIPXSWT 24 SS COR WHTR CONN	24"	609.6mm

### Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

