


Type _____
-15WB

- P2823
- P2824
- P2825
- P2826

Catalog No.	Finish	Lamping	Dimensions (Inches)			
	Polished Chrome		A	B	C	D
P2823	-15WB	1 Halogen (G9, 120V) 35w (included)	7-1/2	5-1/2	4-1/2	2-3/4
P2824	-15WB	2 Halogen (G9, 120V) 35w (included)	14-7/8	5-1/2	4-1/2	2-3/4
P2825	-15WB	3 Halogen (G9, 120V) 35w (included)	22-1/4	5-1/2	4-1/2	2-3/4
P2826	-15WB	4 Halogen (G9, 120V) 35w (included)	29-3/4	4-1/2	2-3/4	



Specifications:

General

- Clear textured glass with etched diffuser panels
- Polished Chrome -15 plated finish
- Steel construction
- Companion Bath and Vanity, fixtures are available

Electrical

- Wedge base sockets (G9)
- Pre-wired

Labeling

- cCSAus Damp location listed

Mounting

- Wall mount
- Back plate covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included