



SUBMITTAL INFORMATION

Straight Ball Yoke Valves - (B91-xxxW-NL style)



FEMALE IRON PIPE THREAD INLET BY METER YOKE NOSE OUTLET



VALVE SIZE	SERVICE LINE SIZE INLET	METER SIZE OUTLET	LENGTH	APPROX. WT. LBS	PART NUMBER	✓ SUBMITTED ITEM(S)
5/8"	3/4"	5/8"	3-11/64"	1.2	B91-213W-NL	
5/8"	3/4"	5/8"x3/4" & 3/4"	3-11/64"	1.2	B91-223W-NL	
3/4"	3/4"	5/8"x3/4" & 3/4"	3-19/32"	1.8	B91-323W-NL	
3/4"	1"	5/8"x3/4" & 3/4"	3-23/32"	1.8	B91-324W-NL	
3/4"	1"	1"	3-31/32"	2.2	B91-344W-NL	
1"	1"	1"	4-1/64"	2.5	B91-444W-NL	

Note: 5/8" ball valves do not have a reinforced seat.

FEATURES

- All brass that comes in contact with potable water conforms to AWWA Standard C800 (ASTM B584, UNS C89833)
 - The product has the letters "NL" cast into the main body for lead-free identification
 - Certified to NSF/ANSI Standard 61 and NSF/ANSI Standard 372 where applicable
 - Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B62 and ASTM B584, UNS C83600, 85-5-5-5)
 - Padlock wing for locking valve in closed position
 - Valve is non-directional and is watertight with flow in either direction
 - Ends are integral or secured with adhesive to prevent unintentional disassembly
 - Hole for attaching handle is provided in the tee-head
 - 300 PSI working pressure
 - EPDM rubber yoke nose gasket sold separately: GT-112 (5/8"), GT-118 (3/4") and GT-123 (1")
- Optional full 360° tee-head rotation.** Add "R" to end of part number. Example: B91-344WR-NL

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.
P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443
Phone: 260-563-3171 / Fax: 800-826-3487
Overseas Fax: 260-563-0167
www.fordmeterbox.com

05/17/18

Submitted By: