CAVALCADE - BUILDERS' CHOICE

60 x 29 1/2 x 22 (1525 x 750 x 560) • Fax on Demand #5050

SOAKER MODEL #3860620 WHIRLPOOL MODEL #3860621



AQUATIC ADVANTAGE

- National distribution
- 5 manufacturing facilities
- Private fleet
- Centralized customer service
- Field support
- 24-hour fax-on-demand

COLOR & TRIM OPTIONS

Stock

Almond (C) Bone (C) Linen/Biscuit (C) Sterling Silver (C) White (C)

C = Color Matched Trim

FEATURES

- 8 hydrotherapy jets
- .75 hp pump
- Advanced safety suction system
- Bath-side on/off button
- Sculpted armrests
- Slip-resistant floor
- Center Front drain
- Lucite cast acrylic surface
- Limited 10-year warranty

OPTIONS

- Comfort pillow:
 Biscuit, Black, White
- 1.5kW inline maintenance heater
- Cable drive waste & overflow: Chrome, Oil Rubbed Bronze, Polished Brass, Brushed Nickel, Color Matched (Biscuit, Bone, White)
- Lift & turn waste & overflow:
 Chrome, Oil Rubbed Bronze,
 Polished Brass, Brushed Nickel
- Tile flange
- Optional pump location
- Acrylic skirt: Color Matched

















Builders' Choice Series • Fax on Demand #5050

CAVALCADE


 $60 \times 29 \frac{1}{2} \times 22 (1525 \times 750 \times 560)$ inches (mm)













FEATURES lbs (kg) Dimensional Tolerance ± 3/8". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work.

Type and Model #	Material	Jets	Pump	Heater	Controls	Drain	Pkg. Wt.
Soaker #3860620	Acrylic	0	-	-	-	Center Front	116 (53)
Whirlpool #3860621	Acrylic	8	0.75 HP	1.5kW inline (optional)	Pneumatic	Center Front	166 (75)

DIMENSIONS inches (mm)

Width	Depth	Height	Skirt
Overall / Net	Overall / Net	Overall / Net	Height
60 (1525)	29 ½ (750)	22 (560)/ 20 (510)	-

SUMP DATA inches (mm)

Capacity to Overflow	Min. Operating Capacity	WIDTH @ centerline		DEPTH @	DEPTH @ centerline	
gal (ltr)	gal (ltr)	Тор	Bottom	Тор	Bottom	
90 (341)	50 (189)	63 (1600)	44 ¾ (1135)	37 (940)	33 (840)	

PLUMBING DIMENSIONS inches (mm)

А	Drain to Overflow	Drain Diameter / Clearance
4 (100)	15 ¾ (400)	2 (50) / 1 1/4 (30)

NOTES:

1) Where applicable, utilize cut-out templates packed with unit for deck cutouts.

2) $16 \times 20 (405 \times 510)$ minimum access required at pump/blower location(s).

ELECTRICAL DATA

Component	Specification	Requirement
Pump	.75 HP; 5 AMP; 120 V	15 AMP; 120V, separate circuit; Class A GFCI