

4700 W. 160th St. Cleveland, OH 44135 PH:800-321-9532 FX:800-321-9535 www.oatey.com

STAND-OFF HALF CLAMPS WITH NAILS



TECHNICAL SPECIFICATION: Oatey Stand-Off Half Clamps with Nails provide fast and easy installation for all types of copper tube size (CTS) piping. Stand-Off Half Clamps with Nails eliminate contact between the pipe and framing surface and insulate against sound. Stand-Off Half Clamps with Nails can be used with hydronic heating systems and are available in $\frac{1}{2}$, $\frac{3}{4}$ " and 1" sizes.



APPROVALS AND LISTINGS



IAPMO Listed

PHYSICAL/CHEMICAL PROPERTIES

Material High Impact Polypropylene

Color Gray

Temperature Range -60°F to 160°F

DIRECTIONS FOR USE

Open clamp and snap over tube or piping. Slide into position. Hammer into place. Barbed shank nail will set clamp and ridges will hold securely. Check with local codes to ensure proper spacing requirements for piping support.

COMMON APPLICATIONS

Oatey Stand-Off Half Clamps with Nail provides fast and easy installation and support for all types of piping including copper, CPVC, and PEX.

PRODUCT NUMBER	DESCRIPTION	PACK	CARTON WEIGHT
34286	1/2" Stand-Off Pipe Clamp with Nail (100 per polybag)	500	6 lbs.
34287	34" Stand-Off Pipe Clamp with Nail (100 per polybag)	500	7 lbs.
34288	1" Stand-Off Pipe Clamp with Nail (50 per polybag)	250	7 lbs.
34298	1/2" Stand-Off Pipe Clamp with Nail (500 in 2.Gallon	1	5 lbs.
	Bucket)		
34299	34" Stand-Off Pipe Clamp with Nail (300 in 2.Gallon	1	3 lbs.
	Bucket)		
33900	1/2" Half Clamp with Barbed Nail (900) in Bucket	100	1 lb
33901	34" Half Clamp with Barbed Nail	100	2 lbs.
33902	1" Half Clamp with Barbed Nail	50	1 lb