



Project
Type
Ordering #
Comments

52 Sterling Manor Select BLD7 NI

339210NI7 (Brushed Nickel)

Product Description:

This refined 52 inch Sterling Manor™ Select fan features a classic Brushed Nickel finish and a White Abaster Glass diffuser to create a delicate statement.

Technical Information

Lamp Included:	Included
Weight:	27.5LBS
Glass Description:	WHITE ALABASTER GLASS
Safety Rated:	Dry
Motor Size:	153MM X 15MM
Motor Type:	AC INDUCTION
Blade Pitch:	11
Blade Sweep:	52
Number of Blades:	5
Blade Finish:	ADOBE CREAM,MAPLE
Downrod 1:	1.00 OD X 4.00
Watts:	65/30/10
Amps:	0.55/0.38/0.21
RPM:	200/134/67
CFM:	5275/3579/1849
Primary Control System:	PULL CHAIN
Airflow Efficiency CFM/Watts:	81/119/185
Light Source:	Incandescent
Socket Base:	Candelabra
Number of Bulbs:	3
Lamp Type:	B10
Max Watt:	40W
Finish:	Brushed Nickel