

PFPTBV Series

PVC Two-piece Threaded Ball Valves



Product Features


- Pressure rating: 150 PSI at 73.4° F (23° C)
- Lower torque and easy to operate
- Full port design
- NPT end connection confirms to ANSI B1.20.1
- Not for use with compressed air or gases

Model Numbers

Nom.	SIZE	PFPTBVL		PFPTBVM		PFPTBVP	
		In	mm	In	mm	In	mm
		2-1/2"	63.5	3"	76.2	4"	101.6
thd./in	NPT	8		8		8	
	BSPT	11		11		11	
D		4.53	115	5.30	134.5	7.48	190
D1		3.52	89.5	4.20	106.8	5.61	142.5
d		2.40	61	2.72	69	3.90	99
L		7.99	203	8.96	227.5	11.81	300
L1		7.09	180	8.82	224	10.94	278
H		4.51	114.5	5.06	128.5	6.93	176




PFPTBVM



Product Specifications

NO.	PART	MATERIAL	Q'TY
1	BODY	PVC	1
2	END CONNECTOR	PVC	1
3	BALL	PVC	1
4	STEM O-RING	EPDM,FPM	2
5	STEM	PVC	1
6	HANDLE	ABS	1
7	UNION O-RING	EPDM,FPM	1
8	SEAT	EPDM,PTFE	2



Warranty and Codes

This PROFLO product carries a 1-year limited warranty.