






Compact Fluorescent

Random

Close-To-Ceiling

ENERGY STAR® qualified

Catalog No.	Finish			Lamping	Type			Dimensions (Inches)	
	Brushed Nickel	Polished Chrome	Antique Bronze		-09WB	-15WB	-20WB	A	B
P3687				<input type="checkbox"/>					<input type="checkbox"/>
P3997				<input type="checkbox"/>		<input type="checkbox"/>			<input type="checkbox"/>
P3998									<input type="checkbox"/>
P3999									<input type="checkbox"/>



Specifications:

General

- Alabaster glass (P3687), Etched glass (P3997), Light Umber Etched glass (P3998), Etched Umber Linen glass (P3999) shade: 10", 4" ht.
- Steel construction
- Plated Brushed Nickel (-09WB), Polished Chrome (-15WB) finishes
- Painted Antique Bronze (-20WB) finish
- 13w GU24 self-ballasted GU-24 lamp (included)
- ENERGY STAR® qualified
- Companion Close-to-ceiling, fixtures are available

Mounting

- Ceiling mount
- Ceiling pan covers a standard 4" hexagonal recessed outlet box
- Mounting strap for outlet box included

Electrical

- GU24 base plastic socket
- Pre-wired

Labeling

- cCSAus Damp location listed



Progress Lighting
701 Millennium Blvd.
Greenville, South Carolina
29607

www.progresslighting.com

Rev. 08/13