

Incandescent


Kensington

Mini-Pendant

Туре		
		-77
	P5141	

_				
_		าเ	•	r
	•	ш	Э	

			Dimer	Dimensions (Inches)		
Catalog No.	Forged Bronze	Lamping	<u>A</u>	<u>B</u>	<u>C</u>	
P5141	-77	1 (m) 100w	7	7-1/2	65	



Specifications:

General

- Trumpet shaped frosted caramel swirl glass shade: 7 " dia. x 5-3/4 " ht.
- Two 6", one 12", and two 15" stems with concealed connections are supplied
- Painted Forged Bronze (-77) finish
- Steel construction
- Companion chandelier, foyer, close to ceiling, and bath and vanity fixtures are available

Mounting

- Ceiling mounted on stems
- Canopy covers a standard 4" hexagonal recessed outlet box
- 90 degree swivel included in canopy
- Mounting strap for outlet box included Electrical
 - Medium based ceramic sockets
 - 10 feet of wire supplied
 - Pre-wired

<u>Labeling</u>

• UL-CUL listed

Progress Lighting 701 Millennium Blvd. Greenville, South Carolina 29607

www.progresslighting.com 2/10