


Type _____
 -30
 PE008 ☐
 PE009 ☐

Catalog No.	Finish	Letters	Wattage	
	White		120VAC	277VAC
PE008	-30	Red	1.78W	1.88W
PE009	-30	Green	1.49W	1.57W



Specifications:

General

- White housing made of high impact UL flame rated thermoplastic
- Universal single- or double-face
- Molded-in template for quick installation
- Snap together canopy, housing, and removable chevrons for quick and easy installation
- Long-life Light Emitting Diode (LED) lamps provide maximum lamp life and energy savings
- 2 Year Warranty

Mounting

- Top, end, or surface mounted
- Snap-in canopy for end or top mounting
- Canopy or housing covers a standard recessed 4" octagonal outlet box.
- Canopy included

Electrical/Battery

- Dual-voltage 120 or 277V AC input
- Includes long-life Nickel Cadmium battery for UL recognized 90-minute emergency lighting
- Test switch with LED charge indicator / AC voltage indicator
- LED life cycle of more than 10 years

Labeling

- UL damp location listed
- UL924 listed
- Meets Life Safety NFPA 101 and NFPA 70 requirements
- Meets OSHA requirements