System 9RLFCC Submittal

AOU9RLFC, AUU9RLF Compact Cassette






Job Name:	Approval:Date:			
	Construction:			
Engineer:	Unit #:			
Submitted to:	Drawing #:			
Submitted by:	Reference:			

Outdoor Unit Power			208-230/VAC-1Ph-60Hz
Available Voltage Range			187-253VAC
Fuse Size, Max.			15A
MCA			13.4A
Compressor	Inverter D	Oriven Va	riable Speed DC Rotary
No. used			1
Output			850W
Lubrican Oil			POE (RB68)
Fan type Motor Output			Propeller 115W
•	g/Heating	(High)	794 / 989 CFM
-	g/i icating	(High)	410A
Refrigerant Outdoor Unit			2lbs 10oz
Contriol		Fle	ctronic Expansion Valve
O.D. Discharge	(in)		1/4"(Flare)
O.D Suction	(in)		3/8"(Flare)
Dimensions	` '		HxWxD
Uncrated	(in)	24-	1/2 x 31-3/32 x 11-11/32
	(mm)		(620 x 790 x 290)
Crated	(in)	28-	1/16 x 37-7/32 x 15-9/16
	(mm)		(713 x 945 x 395)
Weight			Outdoor
Net			84lbs (38kg)
Gross Shipping			93lbs (42kg)
Cooling			0.000DTI.#
Rated Capacity Min-Max Capacity			9,000BTU/h 3,100~12,000BTU/h
Rated Power Input			0.62kw
Max. Power Input			1.40kw
SEER			24
Outdoor Sound Rating			48dB
Heating			
Rated Capacity			12,000BTU/h
Min-Max Capacity			3,100~18,000BTU/h 0.89kw
Rated Power Input Max. Power Input			1.80kw
HSPF			13
Outdoor Sound Rating			49dB
Piping Lengths			_
Max. Piping Length (Total			66ft
Max. Pipe Height Differer Connection method	ice		49ft (Flared)
Operating Range			(Flaieu)
Cooling			





Fujitsu General America, Inc. Fairfield, NJ 07004 Toll Free: 1-888-888-3424

Fax: (973) 836-0447 www.fujitsugeneral.com

Cooling

Heating

Fujitsu products are subject to continuous improvements. Fujitsu reserves the right to modify product design, specifications and information in this data sheet without notice and without incuring any obligations.

14°F~115°F DB -5°F~75°F DB




Power	V/Hz/P	230/60/1	Cooling Capacity	(I
	V/11Z/1		Moisture Removal	ŗ
Fan type No. Motors CFM Sound Pressure Level F.L. A.	(W) (Hi,Me,Lo,Qu) db (Hi,Me,Lo,Qu) (A)	42-1 42-1 318/288/259/230 33/31/29/27 .15	Heating Capacity Temperature Setting Range	<u>(I</u>
Refrigerant		410A	Cooling	•
O.D. Discharge O.D. Suction	in (mm) in (mm)	1/4"(6.35) 3/8"(9.52)	<u>Heating</u>	_
			Drain Pipe Size	(
Dimensions Unit Uncrated	(in) 9-21/32	H x W x D x 22-14/32 x 22-14/32		ı
	(mḿ)	(245x570x570)	Condensate Pump Lift*	
Unit Crated	(in) 10-7/1 (mm)	6 x 28-3/4 x 24-19/32 (265x730x625)	Remote Control Type	
Panel Uncrated	`(in)′ 1-15/1	6 x 27-9/16 x 27-9/16	Electrical Connection**	
Panel Crated	(mm) (in) 4-23/3	(49x700x700) 32 x 30-1/8 x 29-23/32	*D : 11 (:::	na
- unci oratea	(mm) + 20/0	(120x765x755)		_
Weight Unit Net Unit Gross Shipping Panel Net Panel Gross Shipping	lbs. (kg) lbs. (kg) lbs. (kg) lbs. (kg)	33 (15) 40 (18) 5.7 (2.6) 10 (4.5)	is located at the bottom of the condensate. **Power and communication	
(%)	Grille (sold s	seperately)		

Cooling Capacity	(BTU/h)	9,000			
Moisture Removal	pt/h (l/h)	1.3 (0.6)			
Heating Capacity	(BTU/h)	12,000			
Temperature Setting Range					
Cooling	°F(°C)	64~90 (18~32)			
Heating	°F(°C)	60~88 (16~31)			
Drain Pipe Size	OD in (mm)	Ø1 (25.4)			
	ID in (mm)	Ø3/4 (19.4)			
Condensate Pump Lift*	in (mm)	28 (700)			
Remote Control Type		Wired (Wireless Optional)			
Electrical Connection**	AWG	14/3 with ground			
*Pump is capable of providing 28" of lift at no more than 6" away					
from the unit. Lift is measured from the suction of the numn which					

from the unit. Lift is measured from the suction of the pump which is located at the bottom of the unit and not the outlet of the condensate.

*Power and communication are fed from the outdoor unit.



Note:

Specifications are based on the following conditions.

Power source of specifications : 230V

Cooling: Indoor temperature of 80°F(26.67°C)DB / 67°F(19.44°C)WB, and outdoor temperature of 95°F(35°C)DB/75°F(23.89°C)WB. Heating: Indoor temperature of 70°F(21.11°C)DB / 60°F(15.56°C)WB, and outdoor temperature of 47°F(8.33°C)DB/43°F(6.11°C)WB. Standard Static Pressure: 0.10in.WG (25Pa)

Pipe length: 16.4ft. (5m) [Outdoor unit - Branch box], 9.8ft. (3m) [Branch box - Indoor unit]

Height difference : 0 ft.(0m) [Outdoor unit - Indoor unit]

Fujitsu General America, Inc. Fairfield, NJ 07004 Toll Free: 1-888-888-3424 Fax: (973) 836-0447 www.fujitsugeneral.com

Fujitsu products are subject to continuous improvements. Fujitsu reserves the right to modify product design, specifications and information in this data sheet without notice and without incuring any obligations.