

SPECIFICATIONS

AMALFI™ SINGLE HANDLE PRESSURE BALANCE TUB & SHOWER TRIM KIT

Model

D512030T (Tub & Shower trim)
D512530T (Shower only trim)

Description

- 4 1/2" Mono Chic® showerhead D460058
- 6" metal showerarm
- Diverter on spout
- Use with valve D1120 series (w/stops)
or D1150 series (w/o stops) or D1125 series (w/stops)
or D1155 series (w/o stops)
- 2.0 gpm (7.6 L/min) maximum flow rate @ 80 psi

Standards



• UPC/cUPC



• ASME A112.18.1M/A112.18.1




• ADA Accessibility Guidelines for
Buildings and Facilities -
309.4 Operation for Operable Parts

Warranty


Danze products are covered by a manufacturer's
limited "lifetime" warranty for manufacturing defects.

Flow Rate



Finishes Available

- Chrome
- Other: Refer to Price List
for additional finish



Submittal Information:

Job Name: _____
Contractor: _____

Location: _____
Contact #: _____