

Features

- Brass construction.
- Single-hole mounting.
- Above-counter valve for easy installation and maintenance.
- Vandal-resistant aerator.
- 24" (610 mm) flexible supply hoses for easy installation.
- 6-3/16" (157 mm) spout reach.
- Stationary gooseneck spout.
- Includes 30-year Hybrid Energy Cell.
- Less drain.
- 0.35 gal/min (1.32 l/min) maximum flow rate [max at 60 psi (4.14 bar)].
- Meets CalGreen requirements for electronic faucets.
- Complies with "Buy American Act".

Optional Accessories

K- 7129-A Drain
K- 7129 Drain
13478-A
13479-A
13601
1049937 Small Spray 0.5 gpm (1.9 l/min)



ADA

CSA B651

Codes/Standards

ASME A112.18.1/CSA B125.1
NSF 372
DOE - Energy Policy Act 1992
ADA
CSA B651
All applicable US Federal and State material regulations

KOHLER® Electronic Faucets, Valves, and Controls - Five-Year Limited Warranty


See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description

 CP Polished Chrome



Technical Information

All product dimensions are nominal.

Valve body: Cast Brass
Spout reach: 6-3/16" (157 mm)

Faucet:

Flow rate: 0.38 gal/min (1.4 l/min)
Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

A 1-1/4" (32 mm) minimum to 1-1/2" (38 mm) maximum diameter mounting hole is required.

The minimum distance between the back of the faucet spout and the wall must be 1-3/4" (44 mm). This will allow proper clearance for setscrew access.

The maximum distance between the bathroom sink basin edge to the base of the faucet spout must be 1-3/4" (44 mm).

The maximum height of the lip basin should be 3/4" (19 mm).

Product includes rosebud spray aerator. Other aerator styles are available.

ADA, CSA B651 compliant when installed to the specific requirements of these regulations.