

Type B Gas Vent Systems

# **Edition 5**

010



Hart & Cooley, Inc. 5030 Corporate Exchange Blvd. SE Grand Rapids, MI 49512 info@hartcool.com www.hartandcooley.com

 $\begin{array}{ccccc} 800.433.6341 & p \\ 616.656.8200 & p \\ 800.223.8461 & f \\ 616.656.6399 & f \end{array}$ 

#### Order information:

To order Hart & Cooley products, please contact any authorized Hart & Cooley distributor or call 800.433.6341.

When you purchase Hart & Cooley products, you also receive the full support of Hart & Cooley technical and customer service.

#### Technical and customer service:

800.433.6341 toll-free 616.656.8200 phone 800.223.8461 toll-free fax 616.656.6399 fax

#### Internet address:

http://www.hartandcooley.com

#### Install confidence with these other quality

- Hart & Cooley products available:
- Grilles, Registers & Diffusers
- Type B Gas Vent Systems
- Special Gas Vent
- Model TLC All-Fuel Chimney
- Flexible Duct Systems

### Table of Contents



#### TYPE B GAS VENT SYSTEMS

TTPE D GAS VENT STSTEMS					
CONSTRUCTION FEATURES2					
TYPE B RC	OUND GAS VENT PIPE & FITTINGS				
RP	Round Pipe 3" through 12"3				
RP	Round Pipe 14" through 30"3				
RPA/R18A	Adjustable Length Pipe4				
REA90	90° Adjustable Elbow				
REA60	60°/45° Adjustable Elbow 4				
RE45	45° Elbow				
REA45	45° Adjustable Elbow				
RT	Tee				
RTC	Тее Сар5				
RYF	Wye5				
RDH	Draft Hood Connector				
RHW	Cap 3" through 6"6				
RM	Cap 7" through 12"6				
С	Metal Cap 14" through 30"6				
RN	Increaser6				
CU	Universal Cap 14" through 30"6				
RIX	Universal Increaser/Adapter6				
RIX	Increaser7				
RA	Male Adapter7				
RAA	Male Adapter7				
RRA	Female Adapter7				
RF	Adjustable Roof Flashing Flat to 6/128				
RFA	Adjustable Roof Flashing 6/12 to 12/128				
RTF	Tall Cone Roof Flashing8				
RS	Storm Collar 3" through 6" 9				
RS	Adjustable Storm Collar 7" through 12"				
SC	Adjustable Storm Collar 14" through 30"				
RGS	Gripper Support 3" through 6"9				
RSA	Support Assembly 3" through 12" .10				
SP	Support Plate10				
RPC	Pipe Collar 3" through 8"10				
RWT	Wall Thimble				

RWB	Wall Bracket11
RFS	Firestop Spacer11
SFC	Single-Wall Flexible Gas Vent Connector12
DFC	Double-Wall Flexible Gas Vent Segment12
TYPE B (	OVAL GAS VENT PIPE & FITTINGS
OP	Oval Pipe
OPA	Adjustable Oval Pipe
OES45	Elbow - Standard13
OEF45	Elbow - Flat
ОТ	Standard Oval Tee14
OBC	Tee Support14
OTC	Oval Tee Cap14
OAR	Adapter (oval to round)15
OARA	Oval-to-Round Adapter15
RAO	Round-to-Oval Adapter15
OCP	Plate Spacers15
OBPWS	Hold-Down Plate15
OFS	Firestop Spacers16
OC	4" Oval Cap16
ECW	5" Cap16
OF	Oval Flashing16
OSC	Oval Storm Collar16
Typical Ty	pe B Gas Vent Installations

#### GAS APPLIANCE CHIMNEY LINER SYSTEMS

ALK	Basic Kit
ALKE	Extension Kit
ALK-FS	Insulation Sleeve
ALK-FC	Flex Coupler
FX-PD	Pull Down
ALK-VA	Adapters




#### Type B Gas Vent Systems Give You These Important Advantages

**Safety** of the Hart & Cooley<sup>®</sup> system is assured by the double-wall, air-insulated design and locking joints. Properly installed, the vent cannot come apart through vibration, and offers protection against vent failure or fire hazard. Type B Gas Vent is designed for negative pressure applications and flue gas temperatures not exceeding 400° F above ambient for Category I appliances.

**Durability** is the result of high-quality materials and workmanship, with galvanized outer pipe and aluminum inner pipe providing protection against corrosion and external damage.

**Simple installation** is achieved with a complete line of adjustable fittings and various lengths of pipe. Curled ends lock together for stability and easy assembly. A full set of installation instructions are supplied with all caps and supports.



HART & COOLEY<sup>®</sup> B-VENT complies with the latest Underwriters Laboratories Standard No. 441

This Product is Listed by UNDERWRITERS LABORATORIES INC. and Bears the Mark:







Size	Model Number	Listed Length			
	3RP5	5'			
	3RP4	4'			
	3RP3	3'			
3"	3RP24	24"			
	3RP18	18"			
	3RP12	12"			
	3RP6	6"			
	4RPX5	5'			
	4RPX4	4'			
	4RPX3	3'			
4"	4RPX24	24"			
	4RPX18	18"			
	4RPX12	12"			
	4RPX6	6"			
	5RP5	5'			
	5RP4	4'			
	5RP3	3'			
5"	5RP24	24"			
	5RP18	18"			
	5RP12	12"			
	5RP6	6"			
	6RP5	5'			
	6RP4	4'			
	6RP3	3'			
6"	6RP24	24"			
	6RP18	18"			
	6RP12	12"			
	6RP6	6"			

**RP\* Round Pipe** 3" through 12" Listed Length OD L Lock-Ring Style Model Listed Size Number Length 7RP5 5' 7RP4 4' 7RP3 3' 7" 7RP24 24"

7RP18

7RP12

8RP5

8RP4

8RP3

8RP24

8RP18

8RP12

10RP3

10RP24

10RP18

12RP3

12RP24

12RP18

14R3

14R24

14R18

14R12

16R3

16R24

16R18

16R12

18R3

18R24

18R18

18R12

8"

10"

12"

14"

16"

18"

18"

12"

5'

4'

3'

24"

18"

12"

3'

24"

18"

3'

24"

18"

3'

24"

18"

12"

3'

24"

18"

12"


3'

24"

18"

12"

### RP\* Round Pipe 14" through 30"



Snap-Lock Style

			, 199
Size	Model Number	Listed Length	
	20R3	3'	
20"	20R24	24"	
20	20R18	18"	
	20R12	12"	
	22R3	3'	
22"	22R24	24"	
<b></b>	22R18	18"	
	22R12	12"	
			• 3" t ov
24"	24R3	3'	the
	24R24	24"	les
24	24R18	18"	• 14"
	24R12	12"	joi
			as lis
	26R3	3'	• The
26"	26R24	24"	to
20	26R18	18"	4F
	26R12	12"	pr or
			st
28"	28R3	3'	• Out
	28R24	24"	Siz
	28R18	18"	Siz
	28R12	12"	

30R3

30R24

28R18

30R12

30"

3'

24"

18"

12"

" to 12" pipe and fitting couplers overlap 1<sup>3</sup>/8" when joined together; therefore, assembled length is 1<sup>3</sup>/8" ess than listed length.

14" to 30" sizes overlap 1" when joined together; therefore assembled length is 1" less than listed length.

The allowable minimum clearance to combustibles is 1", except for 4RPX on which clearance is provided by locking band on pipe only when installed in a 2 x 6 stud wall.


Outside Diameter (OD) Sizes 3" through 6" is size plus <sup>1</sup>/2"

Sizes 7" through 30" is size plus 1"

A full set of installation instructions are supplied with caps and supports.








- +Overlap: Minimum 1?"
- Maximum overlap on a 12" length is 10".
- Maximum overlap on an 18" length is 16".







### REA90\* 90° Adjustable Elbow

<b></b> B•∣

Model Number	Size	Dim. A	Dim. B	Dim. C
3REA90	3"	5 <sup>1</sup> /2"	3 <sup>3</sup> /4"	7 <sup>1</sup> /4"
4REA90	4"	6"	4 <sup>1</sup> /4"	8 <sup>1</sup> /4"
5REA90	5"	6 <sup>1</sup> /2"	4 <sup>3</sup> /4"	9 <sup>1</sup> /4"
6REA90	6"	7"	5 <sup>1</sup> /4"	10 <sup>1</sup> /4"
7REA90	7"	7 <sup>3</sup> /4"	6"	11 <sup>3</sup> /4"
8REA90	8"	8 <sup>1</sup> /4"	6 <sup>1</sup> /2"	12 <sup>3</sup> /4"



28R18A

30R18A

### REA60\* 60°/45°


28'

30"


Model Number	Size	Dim. A I.D.	Dim. B O.D.	Dim. C	Dim. D
3REA60	3"	3"	3 <sup>1</sup> /2"	1 <sup>7</sup> /8"	5 <sup>1</sup> /4"
4REA60	4"	4"	4 <sup>1</sup> /2"	2 <sup>1</sup> /8"	5 <sup>1</sup> /2"
5REA60	5"	5"	5 <sup>1</sup> /2"	2 <sup>1</sup> /4"	6"
6REA60	6"	6"	6 <sup>1</sup> /2"	2 <sup>5</sup> /8"	6 <sup>3</sup> /8"

18"

18"








### R45\* 45° Elbow

- 14" elbow is adjustable.
- 16" through 30"

Model Number	Size	Dim. A	Dim. B
14R45	14"	6 <sup>5</sup> /8"	6 <sup>1</sup> /2"
16R45	16"	7"	7"
18R45	18"	<sup>79/</sup> 16 <sup>"</sup>	7 <sup>1</sup> /2"
20R45	20"	8 <sup>1</sup> /2"	8 <sup>5</sup> /8"
22R45	22"	8"	7 <sup>5</sup> /8"
24R45	24"	8 <sup>5</sup> /8"	8 <sup>5/</sup> 16"
26R45	26"	9"	9"
28R45	28"	9 <sup>1</sup> /2"	9 <sup>1</sup> /2"
30R45	30"	10"	10"



### REA45\* 45° Adjustable Elbow




Model Number	Size	Dim. A	Dim. B	Dim. C	Dim. D
7REA45	7"	4 <sup>3</sup> /8"	5 <sub>/8</sub> "	10 <sup>3</sup> /8"	4 <sup>3</sup> /4"
8REA45	8"	4 <sup>5</sup> /8"	2 <sup>7</sup> /8"	11 <sup>1</sup> /8"	4 <sup>3</sup> /4"
10REA45	10"	5"	3 <sup>1</sup> /4"	12 <sup>3</sup> /4"	4 <sup>3</sup> /4"
12REA45	12"	5 <sup>1</sup> /2"	3 <sup>3</sup> /4"	13 <sup>3</sup> / <sub>4</sub> "	4 <sup>3</sup> /4"

\*Denotes UL listing








RT*	Тее					
Model Numbe	r Size	Dim. A	Dim. B	Dim. C	Dim. D	
3RT3	3" x 3" x 3"	7 <sup>1</sup> /2"	4 <sup>1</sup> /2"	6 <sup>1</sup> /4"	4 <sup>1</sup> /2"	
4RT4	4" x 4" x 4"	8 <sup>1</sup> /2"	5"	7 <sup>1</sup> /4"	5"	
5RT5	5" x 5" x 5"	9 <sup>1</sup> /2"	5 <sup>1</sup> /2"	8 <sup>1</sup> /4"	5 <sup>1</sup> /2"	
5RT4	5" x 5" x 4"	9 <sup>1</sup> /2"	5 <sup>1</sup> /2"	8 <sup>1</sup> /4"	5 <sup>1</sup> /2"	
5RT3	5" x 5" x 3"	9 <sup>1</sup> /2"	5 <sup>1</sup> /2"	8 <sup>1</sup> /4"	5 <sup>1</sup> /2"	
6RT6	6" x 6" x 6"	10 <sup>1</sup> /2"	6"	9 <sup>1</sup> /4"	6"	
6RT4	6" x 6" x 4"	10 <sup>1</sup> /2"	6"	9 <sup>1</sup> /4"	6"	
6RT3	6" x 6" x 3"	10 <sup>1</sup> /2"	6"	9 <sup>1</sup> /4"	6"	
7RT7	7" x 7" x 7"	11 <sup>1</sup> /2"	6 <sup>1</sup> /2"	10 <sup>3</sup> /4"	6 <sup>3</sup> /4"	
8RT8	8" x 8" x 8"	12 <sup>1</sup> /2"	7"	11 <sup>3</sup> /4"	7 <sup>1</sup> /4"	
10RT10	10" x 10" x 10"	14 <sup>1</sup> /2"	8"	13 <sup>3</sup> /4"	8 <sup>1</sup> /4"	
12RT12	12" x 12" x 12"	16 <sup>1</sup> /2"	9"	15 <sup>3</sup> /4"	9 <sup>1</sup> /4"	
14RT	14" x 14" x 14"	24"	11 <sup>3</sup> /4"	19 <sup>1</sup> /4"	12	
16RT	16" x 16" x 16"	26"	13"	21 <sup>1</sup> /2"	13 <sup>1</sup> / <sub>4</sub> "	
18RT	18" x 18" x 18"	28 <sup>1</sup> /2"	14 <sup>1</sup> /4"	23 <sup>3</sup> /4"	14 <sup>1</sup> /2"	
20RT	20" x 20" x 20"	30"	15 <sup>1</sup> /2"	26	15 <sup>3</sup> /4"	
22RT	22" x 22" x 22"	33"	16 <sup>3</sup> /4"	28 <sup>1</sup> /4"	17"	
24RT	24" x 24" x 24"	36"	18"	30 <sup>1</sup> /2"	18 <sup>1</sup> / <sub>4</sub> "	
26RT	26" x 26" x 26"	38"	19"	32 <sup>1</sup> /2"	19 <sup>1</sup> / <sub>4</sub> "	
28RT	28" x 28" x 28"	40"	20"	34 <sup>1</sup> /2"	20 <sup>1</sup> / <sub>4</sub> "	
30RT	30" x 30" x 30"	42"	21"	36 <sup>1</sup> /2"	21 <sup>1</sup> / <sub>4</sub> "	
nsion A is installed length						



- Diameter	Model Number	Diameter Size
	3RTC	3"
	4RTC	4"
	5RTC	5"
	6RTC	6"
	7RTC	7"
	8RTC	8"
	10RTC	10"
	12RTC	12"
	14RTCP	14"
	16RTCP	16"
	18RTCP	18"
	20RTCP	20"
	22RTCP	22"
	24RTCP	24"
	26RTCP	26"
	28RTCP	28"
	30RTCP	30"






RYF	* Wye

NIF V	vye
Model Number	Size X / Y / Z
4RYF33	4" / 3" / 3"
4RYF44	4" / 4" / 4"
4RYF43	4" / 4" / 3"
5RYF53	5" / 5" / 3"
5RYF54	5" / 5" / 4"
5RYF43	5" / 4" / 3"
5RYF44	5" / 4" / 4"
6RYF54	6" / 5" / 4"
6RYF53	6" / 5" / 3"
6RYF43	6" / 4" / 3"
6RYF44	6" / 4" / 4"
6RYF63	6" / 6" / 3"
6RYF64	6" / 6" / 4"





### RDH\* Draft Hood Connector

Model Number	Size	Dim. A	Dim. B
3RDH	3"	4 <sup>1</sup> /2"	6"
4RDH	4"	4 <sup>1</sup> /2"	6"
5RDH	5"	4 <sup>1</sup> /2"	6"
6RDH	6"	4 <sup>1</sup> /2"	6"
7RDH	7"	7"	8 <sup>1</sup> /2"
8RDH	8"	7"	8 <sup>1</sup> /2"
10RDH	10"	7"	8 <sup>1</sup> /2"
12RDH	12"	7"	8 <sup>1</sup> /2"

B١

### Type B Round Gas Vent Pipe & Fittings





0 🛱

-Size-

RHW* Cap	
3" through	6"


- Exceptional performance in windy conditions.
- Designed to resist nesting birds.

Model		Dim	Dim.
Number	Size	Α.	В
3RHW	3"	8 <sup>1</sup> /4"	4 <sup>1</sup> /2"
4RHW	4"	9 <sup>1</sup> / <sub>4</sub> "	4 <sup>7</sup> /8"
5RHW	5"	110 <sup>1</sup> /2"	5 <sup>1</sup> /4"
6RHW	6"	11 <sup>1</sup> / <sub>4</sub> "	5 <sup>5</sup> /8"

### C\* Metal Cap 14" through 30"

 Barriers provided in cap opening spaced less than 1" are designed to resist entry of birds.

<ul> <li>Snap-locks onto pipe.</li> </ul>					
Model		Dim	Dim.		
Number	Size	Α.	В		
14C	14"	22"	11"		
16C	16"	25"	12"		
18C	18"	28 <sup>1</sup> /4"	13 <sup>1</sup> /2"		
20C	20"	31 <sup>1</sup> /2"	15"		
22C	22"	34 <sup>1</sup> /2"	16 <sup>1</sup> /2"		
24C	24"	37 <sup>3</sup> /4"	18"		
26C	26"	42"	19 <sup>1</sup> /2"		
28C	28"	44"	21"		
30C	30"	48"	22 <sup>1</sup> /2"		



А

Ħ

F

#### RM\* Cap 7" through 12"

 Barriers provided in cap opening spaced less than 1" are designed to resist entry of birds.


	Model Number	Size	Dim A.	Dim. B
	7RM	7"	14 <sup>1</sup> /8"	6 <sup>7</sup> /8"
	8RM	8"	15 <sup>1</sup> /8"	7"
5	10RM	10"	19 <sup>1</sup> /8"	9"
,	12RM	12"	21 <sup>1</sup> /8"	10 <sup>1</sup> /2"

### CU\* Universal Cap 14" through 30"

- Barriers provided in cap opening spaced less than 1" are designed to resist entry of birds.
- Slips into most B Vent.

Model		Dim	Dim.
Number	Size	Α.	В
14CU	14"	22"	11"
16CU	16"	25"	12"
18CU	18"	28 <sup>1</sup> /4"	13 <sup>1</sup> /2"
20CU	20"	31 <sup>1</sup> /2"	15"
22CU	22"	34 <sup>1</sup> /2"	16 <sup>1</sup> /2"
24CU	24"	37 <sup>3</sup> /4"	18"
26CU	26"	42"	19 <sup>1</sup> /2"
28CU	28"	44"	21"
30CU	30"	48"	22 <sup>1</sup> /2"





#### **RN\* Increaser**

B

Model		Dim	Dim.
Number	Size	Α.	В
3RN4	3" to 4"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
3RN5	3" to 5"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
3RN6	3" to 6"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
3RN7	3" to 7"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
4RN5	4" to 5"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
4RN6	4" to 6"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
4RN7	4" to 7"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
5RN6	5" to 6"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
6RN7	6" to 7"	3 <sup>3</sup> /4"	5 <sup>1</sup> /4"
6RN8	6" to 8"	<sup>33</sup> /4"	5 <sup>1</sup> /4"
7RN8	7" to 8"	3 <sup>7</sup> /8"	5 <sup>3</sup> /8"
8RN10	8" to 10"	3 <sup>7</sup> /8"	5 <sup>3</sup> /8"
8RN12	8" to 12"	3 <sup>7</sup> /8"	5 <sup>3</sup> /8"
10RN12	10" to 12"	3 <sup>7</sup> /8"	5 <sup>3</sup> /8"



### RIX\* Universal Increaser/Adapter

 Adapts and increases from locking ring style, small-diameter vent pipe to new snap-lock largediameter vent pipe.

Model Number	Diameter Size
8RIX14U	8" to 14"
10RIX14U	10" to 14"
10RIX16U	10" to 16"
10RIX18U	10" to 18"
12RIX14U	12" to 14"
12RIX16U	12" to 16"
12RIX18U	12" to 18"
12RIX20U	12" to 20"

\*Denotes UL listing



**RRA\*** Female

 Adapts Hart & Cooley vent to other brands of B vent (ours to theirs).


**Adapter** 



Model Number	Diameter Size	Model Number	Diameter Size
14RIX16	14" to 16"	22RIX24	22" to 24"
14RIX18	14" to 18"	18RIX26	18" to 26"
16RIX18	16" to 18"	20RIX26	20" to 26"
14RIX20	14" to 20"	22RIX26	22" to 26"
16RIX20	16" to 20"	24RIX26	24" to 26"
18RIX20	18" to 20"	20RIX28	20" to 28"
14RIX22	14" to 22"	22RIX28	22" to 28"
16RIX22	16" to 22"	24RIX28	24" to 28"
18RIX22	18" to 22"	26RIX28	26" to 28"
20RIX22	20" to 22"	22RIX30	22" to 30"
16RIX24	16" to 24"	24RIX30	24" to 30"
18RIX24	18" to 24"	26RIX30	26" to 30"
20RIX24	20" to 24"	28RIX30	28" to 30"

### **RIX\*** Increaser





Model Number	Size	I.D. A	Dim. B
3RRA	3"	3 <sup>3</sup> /4"	6"
4RRA	4"	4 <sup>3</sup> /4"	6"
5RRA	5"	5 <sup>3</sup> /4"	6"
6RRA	6"	6 <sup>3</sup> /4"	6"



в

AI.D.


### RAA\* Male Adapter

• Adapts other brands of B vent to Hart & Cooley vent (theirs to ours).

Model Number	Size	I.D. A	Dim. B
3RAA	3"	<sup>311/</sup> 16"	6"
4RAA	4"	4 <sup>11/</sup> 16"	6"
5RAA	5"	<sup>5<sup>11</sup>/<sub>16</sub>"</sup>	6"
6RAA	6"	6 <sup>11/</sup> 16"	6"
7RAA	7"	7 <sup>11/</sup> 16"	8 <sup>1</sup> /2"
8RAA	8"	<sup>811/</sup> 16"	8 <sup>1</sup> /2"

			8RA	A	8"	811	<sup>/</sup> 16 <sup>"</sup>	8 <sup>1</sup> /2"
Competitive Manufacturer	Pipe Diameter	Airsp	ace		daptei Male	r		apter male
Metalbest	3" - 6" 7" - 8"	1/ <u>/</u> 1/ <u>/</u>		RA	or RPA RA	4†	F	RRA -
Metal Fab	3" - 6" 7" - 8"	1/ <u>/</u> 1/.		RA	or RPA RPA	4†	F	RRA -
AmeriVent	3" - 6" 7" - 8"	1/ <u>/</u> 1/.	2"	RA	or RPA RPA	4†	F	RRA -
Air-Jet	3" - 6" 7" - 8"	3/8 3/8	3"		RAA RAA			-
DuraVent	3" - 6" 7" - 8"	<sup>5/</sup> 1 <sup>5/</sup> 1			RAA RAA		F	RRA -
†RPA, the Adjust	able Length,	can be	e found	d on	page 4			






### **RA\* Male Adapter**

 Adapts other brands of B vent to Hart & Cooley vent (theirs to ours).

	`		,
Model Number	Size	I.D. A	Dim. B
3RA	3"	<sup>39/</sup> 16 <sup>"</sup>	6"
4RA	4"	4 <sup>9</sup> /16 <sup>"</sup>	6"
5RA	5"	<sup>59/</sup> 16 <sup>"</sup>	6"
6RA	6"	<sup>69/</sup> 16 <sup>"</sup>	6"
7RA	7"	<sup>79/</sup> 16 <sup>"</sup>	17 <sup>3</sup> /4"
8RA	8"	8 <sup>9/</sup> 16"	17 <sup>3</sup> /4"




7





RF Adjustable Roof Flashing Flat to 6/12	
← B →     ← C → >	-


Model Number	Size	Dim. A	Dim. B	Dim C.
			6 <sup>1</sup> /8"	14 <sup>3</sup> /4"
3RF	3"	4"		
4RF	4"	5"	7 <sup>3</sup> /8"	16 <sup>3</sup> /8"
5RF	5"	4 <sup>9</sup> /16"	8 <sup>5</sup> /8"	17 <sup>15</sup> /16"
6RF	6"	6	10"	18 <sup>3</sup> / <sub>4</sub> "
7RF	7"	6 <sup>5</sup> /8"	11 <sup>1</sup> /8"	20
8RF	8"	6 <sup>5</sup> /8"	13 <sup>1</sup> /8"	21
10RF	10"	7 <sup>1</sup> /8"	15 <sup>5</sup> /8"	24 <sup>1</sup> /8"
12RF	12"	7 <sup>5</sup> /8"	18"	25 <sup>1</sup> / <sub>16</sub> "
14RF	14"	9	21"	28
16RF	16"	9	23 <sup>1</sup> /4"	30 <sup>1</sup> /8"
18RF	18"	10	25 <sup>7</sup> /8"	31 <sup>1</sup> /2"
20RF	20"	10	28 <sup>1</sup> /8"	34"
22RF	22"	11	30 <sup>5</sup> /8"	34 <sup>1</sup> /2"
24RF	24"	11	32 <sup>7</sup> /8"	37
26F	26"	12	NA	43
28F	28"	12	NA	45
30F	30"	13	NA	46



### RFA Adjustable Roof Flashing 6/12 to 12/12

NA = Not Available


• Available in 3" through 8"



Model Number	Size	Dim. A	Dim. B	Dim C.
3RFA	3"	5 <sup>1</sup> /2"	6"	7 <sup>1</sup> /4"
4RFA	4"	5 <sup>3</sup> /8"	7 <sup>3</sup> /8"	7 <sup>9</sup> /16"
5RFA	5"	5 <sup>5</sup> /8"	8 <sup>5</sup> /8"	8 <sup>5</sup> /8"
6RFA	6"	5 <sup>3</sup> /8"	10"	8 <sup>13</sup> /16"
7RFA	7"	5 <sup>3</sup> /8"	11 <sup>7</sup> /8"	9 <sup>3</sup> /4"
8RFA	8"	5 <sup>1</sup> /4"	13"	<sup>101</sup> /16"



### RTF Tall Cone Roof Flashing



Model		Dim	Dim.
Number	Size	Α.	В
3RTF	3"	11"	7 <sup>1</sup> /2"
4RTF	4"	11"	7 <sup>1</sup> /2"
5RTF	5"	11"	7 <sup>1</sup> /2"
6RTF	6"	11"	7 <sup>1</sup> /2"
7RTF	7"	11"	11"
8RTF	8"	11"	11"
10RTF	10"	11"	16'
12RTF	12"	11"	16"
14RTF	14"	11"	19 <sup>1</sup> / <sub>4</sub> "
16RTF	16"	11"	19 <sup>1</sup> / <sub>4</sub> "
18RTF	18"	11"	23 <sup>5</sup> /8"
20RTF	20"	11"	23 <sup>5</sup> /8"
22RTF	22"	11"	27 <sup>5</sup> /8"
24RTF	24"	11"	27 <sup>5</sup> /8"
26FT	26"	11"	<sup>319/</sup> 16"
28FT	28"	11"	<sup>319/</sup> 16"
30FT	30"	11"	<sup>319/</sup> 16"





Size

3"

4"

5"

6"

Dim.

Α 3<sup>1</sup>/2"

4<sup>1</sup>/2"

5<sup>1</sup>/2"

6<sup>1</sup>/<sub>2</sub>"

Dim.

В

6<sup>5</sup>/8"

75/8"

85/8"

9<sup>5</sup>/8"

Model

Number


3RS

4RS

5RS


6RS

RS	S Storm	Collar
3"	throug	h 6"




|--|

### **RS** Adjustable **Storm Collar** 7" through 12"



Model Number	Size	Dim. A	Dim. B
7RS	7"	8"	10 <sup>7</sup> /8"
8RS	8"	9"	11 <sup>7</sup> /8"
10RS	10"	11"	14 <sup>1</sup> /2"
12RS	12"	13"	16 <sup>1</sup> /2"

Model Number	Size	Dim. A	Dim. B
7RS	7"	8"	10 <sup>7</sup> /8"
8RS	8"	9"	11 <sup>7</sup> /8"
10RS	10"	11"	14 <sup>1</sup> /2"
12RS	12"	13"	16 <sup>1</sup> /2"



6		
	Len	2

### SC Adjustable **Storm Collar** 14" through 30"

- Designed to be snug around vent pipe for a weather-tight fit.
- For use with roof flashing and caulk.


Model Number	Size	Dim. A	Dim. B
14SC	14"	15"	18 <sup>7</sup> /8"
16SC	16"	17"	21 <sup>1</sup> / <sub>4</sub> "
18SC	18"	19"	23 <sup>1</sup> /4"
20SC	20"	21"	<sup>25<sup>15</sup>/<sub>16</sub>"</sup>
22SC	22"	23"	<sup>285/</sup> 16 <sup>"</sup>
24SC	24"	25"	<sup>30<sup>11</sup>/16"</sup>
26SC	26"	27"	<sup>331/</sup> 16 <sup>"</sup>
28SC	28"	29"	<sup>351</sup> /16"
30SC	30"	31"	<sup>371</sup> /16"

# В

### **RGS\* Gripper Support** 3" through 6"

- Supports 30 feet of pipe.
- Acts as a firestop.
- 7", 8" and 10" not UL-listed.

A Diameter




Model Number	Size	Dim. A	Dim. B	Dim. C Square
3RGS	3"	3 <sup>1</sup> /2"	5 <sup>1</sup> /2"	9"
4RGS	4"	4 <sup>1</sup> /2"	6 <sup>1</sup> /2"	10"
5RGS	5"	5 <sup>1</sup> /2"	7 <sup>1</sup> /2"	11"
6RGS	6"	6 <sup>1</sup> /2"	8 <sup>1</sup> /2"	12"
7RGS	7"	7 <sup>1</sup> /2"	-	13"
8RGS	8"	8 <sup>1</sup> /2"	-	14"
10RGS	10"	10 <sup>1</sup> /2"	-	16"






### RSA\* Support Assembly 3" through 12"

- Supports 30 feet of pipe.
- Acts as a firestop.




Model Number	Size	Dim. A
3RSA	3"	5 <sup>5</sup> /8"
4RSA	4"	6 <sup>5</sup> /8"
5RSA	5"	7 <sup>5</sup> /8"
6RSA	6"	8 <sup>5</sup> /8"
7RSA	7"	10 <sup>1</sup> /8"
8RSA	8"	11 <sup>1</sup> /8"
10RSA	10"	13 <sup>1</sup> /8"
12RSA	12"	15 <sup>1</sup> /8"




### **SP\* Support Plate**

• Supports 30 feet of pipe.




Model Number	Size	Dim. A	Dim. B
14SP	14"	22	14 <sup>5</sup> /8"
16SP	16"	24	16 <sup>5</sup> /8"
18SP	18"	26	18 <sup>5</sup> /8"
20SP	20"	28	20 <sup>5</sup> /8"
22SP	22"	30	22 <sup>5</sup> /8"
24SP	24"	32	24 <sup>5</sup> /8"
26SP	26"	34	26 <sup>5</sup> /8"
28SP	28"	36	28 <sup>5</sup> /8"
30SP	30"	38	30 <sup>5</sup> /8"




### RPC Pipe Collar 3" through 8"

• To cover a rough opening.




Model Number	Size	Dim. A	Dim. B
3RPC	3"	3 <sup>5</sup> /8"	8 <sup>3</sup> /4"
4RPC	4"	4 <sup>5</sup> /8"	8 <sup>3</sup> /4"
5RPC	5"	5 <sup>5</sup> /8"	10 <sup>7</sup> /8"
6RPC	6"	6 <sup>5</sup> /8"	12 <sup>7</sup> /8"
7RPC	7"	8 <sup>1</sup> /8"	14 <sup>7</sup> /8"
8RPC	8"	9 <sup>1</sup> /8"	16 <sup>7</sup> /8"





### **RWT Wall Thimble**

- Provides necessary clearance to combustibles.
- Sleeve is adjustable from 3?" to 6?".



Model Number	Size	Dim. A	Dim. B	Dim. C
3RWT	3"	5 <sup>1</sup> /2"	<sup>31/</sup> 16"	<sup>39/</sup> 16"
4RWT	4"	6 <sup>1</sup> /2"	<sup>31/</sup> 16"	4 <sup>9/</sup> 16"
5RWT	5"	7 <sup>1</sup> /2"	<sup>31/</sup> 16"	<sup>59/</sup> 16"
6RWT	6"	8 <sup>1</sup> /2"	3 <sup>1</sup> /4"	6 <sup>9</sup> /16"
7RWT	7"	10"	3 <sup>1</sup> /4"	<sup>81/</sup> 16"
8RWT	8"	11"	3 <sup>1</sup> /4"	<sup>91</sup> /16"




3" through 7"




8" through 12"

### **RWB Wall Bracket**

- Available in 3" through 12".
- 8" through 12" bracket used with perforated pipe strap supplied by others.




Model Number	Size	Dim. A	Dim. B	Dim. C
3RWB	3"	3"	3 <sup>1</sup> /2"	3 <sup>1</sup> /4"
4RWB	4"	4"	4 <sup>1</sup> /2"	3 <sup>3</sup> /4"
5RWB	5"	5"	5 <sup>1</sup> /2"	4 <sup>1</sup> / <sub>4</sub> "
6RWB	6"	6"	6 <sup>1</sup> /2"	4 <sup>3</sup> /4"
7RWB	7"	7"	8"	5 <sup>1</sup> /2"
8RWB	8"	8"	-	-
10RWB	10"	10"	-	-
12RWB	12"	12"	-	-



### **RFS\*** Firestop Spacer

- Fits 2" x 6" wall.
- Available in 4" only.
  - For other firestops, see installation instructions.








### SFC Single-Wall Flexible Gas Vent Connector

- Single-wall flexible construction.
- Includes an integral appliance draft hood connector for fast installation.
- <sup>2</sup> Locks onto Hart & Cooley Type B gas vent.
- Requires only 1" clearance to combustibles per installation instructions.
- UL-listed for use as a connection from an appliance to Type B gas vent in conditioned spaces only. Do not enclose.
- Available in 3" through 5" diameters and 1' through 5' lengths.

Diameter	Model Number	Length
	3SFC12	12"
	3SFC24	24"
3"	3SFC3	36"
	3SFC4	48"
	3SFC5	60"
	4SFC12	12"
	4SFC24	24"
4"	4SFC3	36"
	4SFC4	48"
	4SFC5	60"
	5SFC12	12"
	5SFC24	24"
5"	5SFC3	36"
	5SFC4	48"
	5SFC5	60"



### DFC Double-Wall Flexible Gas Vent Segment

- Features double-wall, airinsulated construction.
- Has Type B male/female ends for easy connection with Hart & Cooley vent.
- Requires only 1" clearance to combustibles.
- UL-listed for use as a connection from an appliance to Type B gas vent and as a segment of Type B gas vent.
- Can be used in unconditioned spaces, such as attics and crawl spaces. Do not enclose.
- Available in 3" through 5" diameters and 2' through 5' lengths.

Diameter	Model Number	Length
	3DFC24	24"
3"	3DFC3	36"
5	3DFC4	48"
	3DFC5	60"
	4DFC24	24"
4"	4DFC3	36"
4	4DFC4	48"
	4DFC5	60"
	5DFC24	24"
5"	5DFC3	36"
0	5DFC4	48"
	5DFC5	60"





#### TYPE B

Sizes 4" and 5" may be installed with 1" minimum clearance to combustibles.

#### TYPE BW (recessed heater)

Four-inch oval vent (when installed in 2 x 4 stud wall with recessed heater) requires clearances as determined by use of 4OBPWS hold-down plate, 40CP ceiling plate spacers, and 40FS firestop spacers.

#### TYPE B 2x4

Four- and five-inch oval vent (when installed in 2 x 4 stud wall, not using a recessed heater) requires clearance as determined by use of 4OFS or 5OFS firestop spacers at each ceiling level.

### **OP Oval Pipe**


· Offers all the advantages of round pipe, and may be used for the following types of installation.

#### 4" Oval:

Conventional Type B Type B-2x4 when used with firestop Type BW-2x4 with recessed heater

### 5" Oval: Type B

Type B-2x4



18,24,3,4,5				
Model Number	Size	Dim. A	Dim. B	
40P_*_	4"	7 <sup>1</sup> /16"	2 <sup>7</sup> /8"	
50P_*_	5"	10 <sup>3</sup> / <sub>4</sub> "	2 <sup>7</sup> /8"	
*Add length to complete Model Number.				

Lengths for 4" Sizes: 6", 12", 18", 24", 3', 4', 5'

Lenaths for 5" Sizes:

### **OPA Adjustable Oval Pipe**

The adjustable length telescopes onto standard pipe sections to permit adjustments from 3" to 10".

#### Sizes for 12" Lengths: 4", 5" (adjustable from 3" to 10")

Model Number	Size
40PA	4"
50PA	5"



#### **OES45** Elbow – Standard

The standard 45° elbow is used in pairs where offsets are desired in 1" minimum clearance enclosures or open spaces, such as attics or basements. Add pipe sections between pairs to produce additional offset.

Model Number	Size	Dim. A	Dim. B
40ES45	4"	3"	3"
50ES45	5"	3 <sup>1</sup> /2"	3 <sup>1</sup> /2"







#### **OEF45 Elbow – Flat**

 The flat 45° elbow is used in pairs where offsets are desired in 1" minimum clearance enclosures or open spaces, such as attics or basements. Add pipe sections between pairs to produce additional offset.


Model Number	Size	Dim. A	Dim. B
40EF45	4"	3 <sup>3</sup> /4"	3 <sup>3</sup> /4"
50EF45	5"	4 <sup>3</sup> /4"	4 <sup>3</sup> /4"



#### OT Standard Oval Tee

The branch size and trunk size have the same diameter. The tee branch accepts either double- or single-wall pipe.

Model Number	Size	Dim. A	Dim. B	Dim. C
40T	4"	12"	<sup>29</sup> /16"	2 <sup>3</sup> /8"
5OT	5"	12"	<sup>29</sup> / <sub>16</sub> "	2 <sup>3</sup> /8"



### **OBC Tee Support**

B

The tee support is used to support and center the tee. Use with the tee cap shown below.

Model Number	Size
40BC	4"
5OBC	5"



### OTC Oval Tee Cap

 The tee cap is used for closing off the bottom of the tee.

Model Number	Size
4OTC	4"
5OTC	5"





### OAR\* Adapter (oval to round)

 Adapts from snaplock oval to lockring style round.

	1			λ
1	1			
Ą			/	/
	5	/		

Model Number	Size	Dim. A
40AR	4"	11 <sup>3</sup> /8"



#### OARA Oval-to-Round Adapter

- The oval-to-round adapter is used for conversion of vent from oval to round.
- Requires use of RAA male adapter to continue with round.

Model Number	Size	Dim. A
40ARA	4"	6 <sup>7</sup> /8"
50A5RA	5"	9 <sup>3</sup> /8"



### RAO Round-to-Oval Adapter

- The round-to-oval adapter is used for conversion of vent from round to oval.
- Requires use of RRA female adapter to come from round.

Model Number	Size	Dim. A
4RAO	4"	6 <sup>7</sup> /8"
5RA5O	5"	9 <sup>3</sup> /8"



### **OCP Plate Spacers**

 Type BW plate spacers are required at the first ceiling level above a wall furnace to center and space vent properly and to provide the required opening between floors. Firestop spacers must be used at subsequent levels.

Model Number	Size
40CP	4"



### **OBPWS Hold-Down Plate**

The Type BW hold-down plate is required for connecting Type BW vent to a wall furnace outlet.

Model Number	Size
40BPWS	4"





### **OFS Firestop Spacers**

 The firestop spacers center vent in 16" O.C. stud space and serve as a firestop at the ceiling level. This is a required component for Type B 2 x 4 and multi-story Type BW installations.

Model Number	Size	Wall
40FS	4"	2" x 4"
50FS	5"	2" x 4"
4OFS6	4"	2" x 6"



#### OC 4" Oval Cap




Model Number	Size	Dim. A	Dim. B
OC	4"	5 <sup>3</sup> /8" x 8 <sup>1</sup> /2"	3 <sup>1</sup> /2"



### ECW 5" Cap

Requires use of 50A5RA.



Model Number	Size	Dim. A	Dim. B
5ECW	5"	9 <sup>7</sup> /8"	<sup>5<sup>5/</sup>16<sup>"</sup></sup>

# • The all-pitch flashing is

• The all-pitch flashing is installed either parallel or perpendicular to the roof ridge, and fits roof pitches flat to 5/12.

Model Number	Size
40F	4"
50F	5"




### **OSC Oval Storm Collar**

 The storm collar serves as a counter flashing and requires mastic to seal to the vent pipe.

Model Number	Size
40SC	4"
5OSC	5"



### **Typical Type B Gas Vent Installations**



### Gas Appliance Chimney Liner Systems





Model Number	Size	Listed Length
3ALK15	3"	15'
3ALK25	3"	25'
3ALK35	3"	35'
4ALK15	4"	15'
4ALK25	4"	25'
4ALK35	4"	35'
5ALK15	5"	15'
5ALK25	5"	25'
5ALK35	5"	35'
55ALK25	5.5"	25'
55ALK35	5.5"	35'
6ALK25	6"	25'
6ALK35	6"	35'
7ALK25	7"	25'
7ALK35	7"	35'
8ALK25	8"	25'
8ALK35	8"	35'

#### **ALK Basic Kit**

- Available in 3", 4", 5", 5.5", 6", 7" and 8" diameters
- Available in 15', 25' and 35' lengths
- UL-listed
- · Compatible with Type B gas vent systems
- Kit includes length, round top, flashing with 3" collar, mortar guard, fasteners and instructions
- \* ALK-FC Flex Coupler is available to assist in joining flexible lengths or connecting to fittings.

\* ALK-VA Type B Gas Vent Adapter is available to transition from Type B Gas Vent to ALK Chimney Liner.

Model Number	Size	Listed Length
3ALKE10	3"	10'
4ALKE10	4"	10'
5ALKE10	5"	10'
55ALKE10	5.5"	10'
6ALKE10	6"	10'
7ALKE10	7"	10'
8ALKE10	8"	10'

### ALKE Extension Kit

- 10' flexible liner length
- Includes coupler and fastener package
- UL-listed



Model Number	Size
4ALK-FS	3"-4"
5ALK-FS	5"
6ALK-FS	5.5"-6"
7ALK-FS	7"
8ALK-FS	8"

### **ALK-FS Insulated Sleeve**

- Insulation sleeve with tough poly exterior
- · Cable ties included

### Gas Appliance Chimney Liner Systems

Model

Number | Size |






Number	0120		
3ALK-FC	3"	4"	2.97"
4ALK-FC	4"	4"	3.97"
5ALK-FC	5"	4"	4.97"
55ALK-FC	5.5"	4"	5.47"
6ALK-FC	6"	4"	5.97"
7ALK-FC	7"	4"	6.97"
8ALK-FC	8"	4"	7.97"

Dim. A Dim. B

### **ALK-FC Flex Coupler**

For fitting or joining ALK liner lengths




Model Number	Size
3FX-PD	3"
4FX-PD	4"
5FX-PD	5"
55FX-PD	5.5"
6FX-PD	6"
7FX-PD	7"
8FX-PD	8"

### **FX-PD Pull Down**

• Used to stretch and lead ALK liner down chimney





### **Adapters**


Adapter to transition from all brands of listed Type B Gas Vent to ALK Liner




### Notes




### Check out other quality Hart & Cooley products...




Form No. 010050




Form No. 851343



Form No. 851369



Form No. 851367



Form No. 010054

To order any of the above catalogs, please contact Customer Service toll-free at 800.433.6341.



 
 Hart & Cooley, Inc.
 800.433.6341 p

 5030 Corporate Exchange Blvd. SE
 616.656.8200 p

 Grand Rapids, MI 49512
 800.223.8461 f

 info@hartcool.com
 616.656.6399 f
 www.hartandcooley.com

Offered by:

## www.hartandcooley.com

For submittal information and other literature visit our Website.

®2008 Hart & Cooley, Inc. All rights reserved

Printed in U.S.A