

# **Specifications**

#### **PRODUCT DESCRIPTION**

- Manual exposed flushometer retrofit
- Cast brass construction with chrome electroplated finish
- Chloramines resistant seals
- 1-1/2" tailpiece nut assembly
- High back pressure vacuum breaker
- ADA compliant handle with dual o-ring seals

#### **OPERATION**

- Operating pressures: 15 to 120 psi
- AccuSet<sup>™</sup> piston technology
- Self-cleaning filter


#### **FLOW**


#### Closet

- □ **8310MR35** (3.5 gpf/13.2 Lpf)
- □ **8310MR16** (1.6 gpf/6.0 Lpf)
- □ **8310MR128** (1.28 gpf/4.8 Lpf)

#### Urinal

- □ **8312MR10** (1.0 gpf/3.8 Lpf)
- ☐ 8312MR05 (0.5 gpf/1.9 Lpf) –WaterSense certified
- ☐ **8312MR0125** (0.125 gpf/0.5 Lpf) **–WaterSense certified**





## ADA 🖶


### WARRANTY

· Warranted for 5 years against material or manufacturing defects



# **Manual Exposed Style Flush Valve Retrofit**





## **CRITICAL DIMENSIONS**

(DO NOT SCALE)