



FASTFIT™ Stops with Risers

Product Features

- Low Lead compliant
- Push style connection
- For use with Copper, CPVC and PEX pipe
- Brass body
- Stainless steel braided EPDM hose
- Quarter Turn operation
- May be removed and re-used
- Temperature range: 40°F - 160°F
- Max pressure: 125 psi
- Meet ANSI/NSF Standard 61 certification



PFXQAQ32CFC12

Part Numbers

| <i>Part #</i> | <i>Description</i> | <i>Finish</i> | <i>Length</i> |
|----------------------|--|---------------|---------------|
| PFXQAQ32CFC12 | LF 5/8 OD X 7/8 Ballcock Angle Stop with Closet Riser | Chrome Plated | 12" |
| PFXQSQ32CFC12 | LF 5/8 OD X 7/8 Ballcock Straight Stop with Closet Riser | Chrome Plated | 12" |
| PFXQAQ32CFL20 | LF 5/8 OD X 1/2 F Angle Stop with Lavatory Riser | Chrome Plated | 20" |
| PFXQSQ32CFL20 | LF 5/8 OD X 1/2 F Straight Stop with Lavatory Riser | Chrome Plated | 20" |

Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

