

PL581912

FEATURES

Heavy-duty stainless steel construction

Infinite speed blower control

Recessed controls for sleeker look

Heat sentry for safety

Bright halogen lighting

Blower required (internal, in-line or remote blowers available)

Transition with backdraft minimizes backward flow of cold air

Rigorously tested in our U.S. manufacturing facilities for decades of use

Exceptional 24/7 support from our Customer Care team in Madison

ACCESSORIES

Make-up air damper

Accessories available through an authorized Sub-Zero dealer.
For local dealer information, visit subzero-wolf.com/locator.



BLOWER OPTIONS

- 300 CFM Internal
- 450 CFM Internal
- 600 CFM Internal
- 900 CFM Internal
- 1200 CFM Internal
- 600 CFM Inline
- 1100 CFM Inline
- 600 CFM Remote
- 900 CFM Remote
- 1200 CFM Remote
- 1500 CFM Remote



PRODUCT SPECIFICATIONS

Model	PL581912
Dimensions	58 3/8"W x 12"H x 19 1/4"D
Weight	80 lbs
Electrical Supply	110/120 VAC, 60 Hz
Electrical Service	15 amp dedicated circuit
Discharge Location	Vertical
Discharge Dimensions	10" Round
Bottom of Hood to Countertop	30" to 36"

NOTE:

Dimensions in parenthesis are in millimeters unless otherwise specified

DIMENSIONS

