14PAR30LN /LED /40' /3500K /WH
14 Watt; PAR30; 3500K; 40' Beam Spread; Medium Base; 120 Volts

Features
- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable

View Dimmer Compatibility



S8948

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S8948	045923089480	14	PAR30	Medium	E26	14PAR30LN /LED /40' /3500K /WH	120

Finish	MOL In Inches	MOL in mm	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	CRI
White	4.5"	114.30 mm	3.69"	890	35000	3500	83

Incandescent Equivalent	Pack	Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed
75	12/6	Box	40	ENERGY STAR	Yes	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas, Washington, California, Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051