# **HALO**®

## DESCRIPTION

The H7 recessed housing is the standard in the industry for both commercial and residential applications. The wide variety of trims available allows a number of different lighting effects to be created with one basic housing. H7ICT is for installations where the housing will be in direct contact with insulation.

Catalog #	Type
Project	
Comments	
Prepared by	Date

## **DESIGN FEATURES**

## A...Housing

Aluminum construction for greater heat dissipation.

## B...Socket Plate

Rigid socket plate adjusts and locks without tools for various lamp sizes.

## C.-Plaster Frame

Housing adjusts in plaster frame to accommodate up to 1-3/4" ceiling thickness. Plaster frame features include:

- · Regressed locking screw for securing hanger bars
- · Cutouts for easily crimping hanger bars in position
- · Halo name embossed on plaster frame Galvanized steel construction. The housing can be removed from plaster frame to provide access to the iunction box.

## D...Junction Box

- · Listed for through branch circuit wiring
- · Positioned to accommodate straight conduit runs
- Seven 1/2" trade size conduit knockouts with true pry-out slots
- Slide-N-Side<sup>™</sup> connectors

allow non-metallic sheathed cable to be installed without tools and without removing knockouts. Accepts a wider range of non-metallic sheathed cable - the standard cable types used in lighting for both U.S. and Canada.

- Allows wiring connections to be made outside the junction
- Simply insert the cable directly into the trap after connections are made
- accommodates the following standard non-metallic sheathed cable types: (US) #14/2, #14/3, #12/2, #12/3 (Canada) #14/2, #14/3, #12/2

## E…GOT NAIL! Pass-N-Thru™ **Bar Hangers**

Bar Hanger Features include:

- Pre-installed nail easily installs in regular lumber, engineered lumber and laminated beams
- Safety and guidance system prevents snagging, ensures smooth straight nail penetration and allows bar hangers to be easily removed if necessary.
- Automatic levelling flange aligns the housing and lets you

hold the housing in place with one hand while driving nails

- Housing can be positioned at any point within 24" joist span
- Score lines allow "tooless" shortening for 12" joists
- Bar hangers may be repositioned 90°
- Bar hangers do not need to be removed from frame for shortening
- Integral T-bar clips snaps onto T-bars - no additional clips required

## F...Socket

Porcelain socket with nickel plated brass screw shell, snaps into trim for consistent lamp positioning.

## G...Thermal Protector

Self resetting thermal protector deactivates fixture if overheating occurs due to improper lamping.

- UL/cUL Listed
- Listed for Damp Location
- Listed for Feed Through
- Listed for Direct Contact with insulation and combustible material



H7ICT 6" Insulated Ceiling **Recessed Housing** 

6" TRIMS

FOR USE IN **INSULATED CEILINGS** 

## FOR DIRECT CONTACT WITH INSULATION

This housing is AIR-TITE when used with the following Trims: 170PS 171PS 173PS 78PAT 30 (All Styles) 430 (All Styles)

ERT712 (All Styles) ERT713 (All Styles) **ERT725 Series** 






## **UPGRADE FEATURES:**

- SLIDE-N-SIDE™ JUNCTION BOX
- GOT NAIL!™ BAR HANGERS
- PASS-N-THRU™ BAR HANGERS • REGRESSED LOCKING SCREW
- HALO ID ON PLASTER FRAME

## ADV042486

Supersedes ADV031581, ADV023106 & ADV000300) TAB: Recessed Incandescent Sheet 17



Top View 7 1/2 [191mm] 10 1/2'

Ordering information on reverse

Slide-N-Side III<sup>T</sup> Junction Box

## ORDERING INFORMATION

## SAMPLE NUMBER: H7ICT-426RG

Order housing, trim and accessories separately.

## Housing

Trims

REFLECTORS

H7ICT=Insulated Ceiling Housing





60W A19, 75W PAR30, 75W R30, 65W BR30, 75W PAR30L, 60W PAR38 30CAT=Specular Clear, Air-Tite

30HAT=Haze, Air-Tite 30RGAT=Residential Gold, Air-Tite 30SNAT=Satin Nickel

7 1/4" (184mm)

AIR-TITE Super Trim



30

AIR-TITE Super Trim 40W A19, 50W PAR30, 50W PAR38, 65W BR30, 75W PAR30L, 75W R30 30SBAT=Specular Black, Air-Tite OD: 7 1/4" (184mm)

Specular Reflector 60W A19



426

404C=Specular Clear 404H=Haze Reflector 404RG=Residential Gold 404SN=Satin Nickel 7 1/4" (184mm)

Specular Reflector Cone 50W PAR30, 75W R30, 65W BR30, 75W PAR30L



426SB=Specular Black 426SN=Satin Nickel 7 1/4" (184mm) **Dayform Cone** 

50W PAR30, 75W R30, 65W BR30, 75W PAR30L 429 429P=White 7 1/4" (184mm)



4261

Self Flanged Reflector 60W A19

4041P=White 7 1/4" (184mm)



4261P=White OD: 7 1/4" (184mm)

## **BAFFLES**



AIR-TITE Super Trim 40W A19, 75W R30, 65W BR30, 60W PAR38, 75W PAR30, 75W PAR30L

30PAT=Black Baffle 30WAT=White Baffle 7 1/4" (184mm)

Baffle

75W R30, 65W BR30, 75W PAR30L, 50W PAR30 310P=Black Baffle

310W=White Baffle 310SN=Satin Nickel Trim Ring, Black Baffle 7 1/4" (184mm)

Baffle 50W PAR30, 65W BR30, 75W PAR30L, 75W R30, 65W BR30 312P=Black Baffle 312W=White Baffle 7 1/4" (184mm)

**ADJUSTABLES** 

310



**Eveball** 75W PAR30 74P=White Eyeball 8" (203mm) OD:

Eyeball 50W R20 77P=White Eveball 8" (203mm) Eyeball 75W R30

OD:

78P=White Eyeball 78SL=Silver Eyeball 78B=Brass Eyeball 78B=Brass Eyeball 78SN=Satin Nickel 78PAT=White Eyeball (converts H7ICT and H7RICT to AIR-TITE Construction)

8" (203mm) Adjustable - 60° Tilt 150W PAR38

90P=White "Double Bubble" OD: 8" (203mm)

Coilex Regressed Eyeball 50W PAR30L, 60W BR30 420P=Black Baffle, White Eyeball

420PB=Black Baffle, Polished Brass Eveball 420W=White Baffle, White Eyeball

7 1/4" (184mm)

### **DIFFUSERS** Glass Albalite Lens



420

78

170P=White Trim Ring 170PS=White Trim Ring, Shower Light 8" (203mm)

Plastic Drop Opal 40W A19

171P=White Trim Ring 171PS=White Trim Ring, Shower Light OD: 8" (203mm)

**Glass Fresnel Lens** 40W A19



172

171

173P=White Trim Ring 173PS=White Trim Ring, Shower Light OD: 8" (203mm)

**Shower Light** 60W A19, 50W PAR30

172PS=White Trim Ring, Shower Light 172SNS=Satin Nickel Trim Ring, Shower Light

OD. 7 3/4" (197mm)

## OPEN



Open 75W R30, 75W PAR30, 75W PAR30L, 65W BR30 300P=White

300SN=Satin Nickel 7 1/4" (184mm)

Splay Trim with Integral socket Support 65W BR30, 75W PAR30, 75W PAR30L 327P=White Splay OD: 7 1/4" (184mm)

327

Splay Trim 75W R30, 75W PAR30, 65W BR30

328P=White Splay OD: 7 1/4" (184mm) OD:

# WALL WASH



328

Baffle Wall Wash 40W A19 430P=Black Baffle, White Scoop, White



### Accessories

Metal Trim Rings Compatible with 310 and 312 TRM6P=White Metal TRM6PB=Polished Brass TRM6C=Chrome TRM6MB=Black Metal

TRM6SL=Silver TRM6SN=Satin Nickel TRP7MB=Black Plastic

**Oversize Trim Rings** For use when ceiling opening is cut too large. Compatible

with 310 and 312 OT400P=9 1/4" White Metal OT403P= 8" White Plastic

Note: Specifications and Dimensions subject to change without notice.