

# Archer® hirlpool Bath

# 5' Whirlpool Bath K-1947-RA

# GREENGUARD PROSUCT CERTIFIC TOTAL LOW OF STATEMENT ENTRANCE ULCOM/CG ULCOM/CG

#### **Features**

- Integral flange.
- Slotted overflow for deep soaking.
- Right drain.
- Integral apron with removable access panel.
- Integral lumbar support.
- Coordinates with other products in the Archer® collection.
- 60" (1524 mm) x 30" (762 mm) x 19" (483 mm)

#### **Material**

Acrylic

## **Hydrotherapy**

- Single-speed whirlpool offers eight fully adjustable hydro-massage jets for water flow and direction.
- Pump with air switch for whirlpool.

#### Installation

Alcove

#### **Required Accessories**

K- 7271 Brass Slotted Overflow Bath Drain or

K-7272 PVC Slotted Overflow Bath Drain

#### **Recommended Accessories**

K- 24916 Wireless Music Kit



#### **ADA**

#### Codes/Standards

ASME A112.19.7/CSA B45.10 CSA B45.5/IAPMO Z124 UL 1795 CSA C22.2 No. 218.2 Greenguard UL 2818 - Gold ADA ICC/ANSI A117.1 CARB P2

# KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

#### Available Color/Finishes

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	NY	Dune
	95	Ice™ Grey
	G9	Sandbar
	33	Mexican Sand™
	K4	Cashmere
	58	Thunder™ Grey
	7	Black Black™








# Archer® 5' Whirlpool Bath K-1947-RA

No change in measurements if connected with drain illustrated. (K-7272)









## **Required Electrical Service**

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump: 120 V, 15 A, 60 Hz

#### **Technical Information**

All product dimensions are nominal. Installation: 3-Wall Alcove

Drain location: Right

Basin area, bottom: 45-1/8" x 19-11/16" (1146 mm x 500 mm) Basin area, top: 52-1/8" x 22-1/16" (1324 mm x 560 mm)

57 gal (215.8 L)

Weight: 113 lbs (51.3 kg)

Minimum floor load: 49 lbs/ft² (239.2 kg/m²)

Water depth: 15-1/8" (384 mm)

Electrical component Pump: 120 V, 7 A, 60 Hz

rating:

Water capacity:

Pump speed: Single

#### **Notes**

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Provide one grounded electrical outlet within 24" (610 mm) of each component.

ADA compliant when installed to the specific requirements of these regulations.

