



Job Name:

Job Type:

Comments:

Quantity:

## 4108-71: Single-Light Costa Wall Sconce



### Dimensions:

Width: 10"

Extends: 5"

Height: 10"

Wire: 6 1/2"

Mounting Proc.: Wall / Bath

Connection: Mounted To Box

### Bulbs:

- 1 - medium A - Line 100w Max. 120v - Not included
- 1 - LED Medium LED A-19 8w 120v - Not included
- 1 - LED Medium LED A-19 13.5w 120v - Not included

### Material List:

1 Trim - Steel - Antique Bronze

### Safety Listing:

UL Listed for Damp Locations  
cUL Listed for Damp Locations

### Instruction Sheets:

English (HC-118)  
French (F-006)

Glowing Example of Artistry in Lighting. This Wall Sconce is Finished in Naturally Beautiful Antique Bronze Solid Brass and Softly Illuminated by Nuage Creme Glass.

Glowing example of artistry in lighting. This wall sconce is finished in naturally beautiful Antique Bronze Solid Brass and softly illuminated by Nuage Creme glass.

UPC #:785652410819

Finish: Antique Bronze (71)

### Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Nuage Creme	1			10	8 3/8					

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	7	4 1/4			4 3/4	5

### Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	4108-71	1	785652410819	13.25	13.25	8.25	0.838	3	Yes
NJ Pallet		96		48	40	76	84.444	350.4	No
NV Pallet		72		48	40	72	80	216	No