

## STEEL YOKE ROLLER HANGER

#### **Features**

- For Pipe Suspension Where Longitudinal Movement Due to Expansion and Contraction Can Occur
- Suspend Pipe from Single Hanger Rod (Hanger Rod and Nuts Not Included)
- Adjustable in Vertical Direction
- · Epoxy Plated Yoke
- · Carbon Steel Yoke, Axle and Nuts
- Cast Iron Roller

### **Standards**

- Design: MSS SP-58 Type 43
  Federal Specification WW-H-17E Type 44
- Selection & Application: MSS SP-69 Type 43




## Model Numbers, Design Loads & Weights

| Catalog Number | Pip | e Size | Desig | Weight |       |  |
|----------------|-----|--------|-------|--------|-------|--|
| Catalog Number | in. | mm     | Lbs.  | kN     | Lbs.  |  |
| FNW7901EP0300  | 3   | 88.9   | 310   | 1.38   | 1.82  |  |
| FNW7901EP0400  | 4   | 114.3  | 475   | 2.11   | 3.24  |  |
| FNW7901EP0500  | 5   | 141.3  | 685   | 3.05   | 5.18  |  |
| FNW7901EP0600  | 6   | 168.2  | 780   | 3.47   | 6.81  |  |
| FNW7901EP0800  | 8   | 219.1  | 780   | 3.47   | 12.16 |  |
| FNW7901EP1000  | 10  | 273.1  | 965   | 4.29   | 18.08 |  |
| FNW7901EP1200  | 12  | 323.9  | 1200  | 5.34   | 23.08 |  |



# STEEL YOKE ROLLER HANGER



## **Dimensions**

| Catalog Number | Pip | e Size | A<br>(Rod Size) | В       |        | С        |        | D       |        | E      |       | F      |        |
|----------------|-----|--------|-----------------|---------|--------|----------|--------|---------|--------|--------|-------|--------|--------|
|                | in. | mm     |                 | in.     | mm     | in.      | mm     | in.     | mm     | in.    | mm    | in.    | mm     |
| FNW7901EP0300  | 3   | 88.9   | 1/2-13          | 2-3/16  | 55.56  | 6-7/8    | 174.63 | 3-1/2   | 88.90  | 2-1/16 | 52.39 | 3-7/8  | 98.43  |
| FNW7901EP0400  | 4   | 114.3  | 5/8-11          | 2-13/16 | 71.44  | 7-5/8    | 193.68 | 3-5/8   | 92.08  | 1-5/8  | 41.28 | 4-7/8  | 123.83 |
| FNW7901EP0500  | 5   | 141.3  | 5/8-11          | 3-3/8   | 85.73  | 9-1/8    | 231.78 | 4-9/16  | 115.89 | 2      | 50.80 | 5-7/8  | 149.23 |
| FNW7901EP0600  | 6   | 168.2  | 3/4-10          | 4       | 101.60 | 10-5/16  | 261.94 | 4-15/16 | 125.41 | 2      | 50.80 | 7      | 177.80 |
| FNW7901EP0800  | 8   | 219.1  | 7/8-9           | 5-1/16  | 128.59 | 12-11/16 | 322.26 | 5-15/16 | 150.81 | 2      | 50.80 | 9      | 228.60 |
| FNW7901EP1000  | 10  | 273.1  | 7/8-9           | 6-1/4   | 158.75 | 15       | 381.00 | 7-1/16  | 179.39 | 2-1/16 | 52.39 | 11-1/8 | 282.58 |
| FNW7901EP1200  | 12  | 323.9  | 7/8-9           | 7-3/8   | 187.33 | 17       | 431.80 | 8-3/8   | 212.73 | 1-7/8  | 47.63 | 13-3/8 | 339.73 |

DOC: FNW790113 Ver. 7/2017

© 2018 - FNW. All rights reserved.

The FNW logo is a trademark of Ferguson Enterprises, Inc., PL Sourcing, PO Box 2778, Newport News, VA 23609

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available on request. We reserve the right to modify or improve the designs or specifications of our products at any time without notice. Always verify that you have the most recent product specifications or other documentation prior to the installation of these products.