

Item #: **P950-084-L**
 Product Family Name: **U. H. O.**
 Category: **Flush Mount**
 Certification: **4006873**
 Patents:
 Notes:

UPC Code: **844349013686**
 Finish: **Brushed Nickel**
 Category Type: **Flush Mount**



Image File Name:
 P950-084-L--
 1377188249.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
15	15	3.5	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	5.07
Canopy Width:	Canopy Height:	Canopy Length:	
6.25	1.75	6.25	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs:	Light Type:			
1	L-Md-C9615c-40w			
Max Bulb Wattage:	Socket:			
40	Led			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes		30000		Yes
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
Yes	3000	98	3115	2224



SHIPPING

Carton Width:	Carton Height:	Carton Length:
17.5	5.5	17.5
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
7.436	0.975	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1

SHADE / GLASS

Description:	Material:
	Acrylic
Part No.:	Quantity:
	1
Width:	Height:
15	1.57
	Length:
	15

LED



LED

ADA
Compliant
Yes

Damp
Location
Yes

ETL Intertek

Yes