

**NIBCO**

1516 Middlebury Street
Elkhart, IN 46516-4740

Phone: 574.295.3000 • **Fax:** 800.234.0557

E-Mail: info@nibco.com • **Web site:** www.nibco.com

Material Number NL94Q7C, T-580-S6-R-66-LL - Two-Piece Stainless Steel Ball Valve - Conventional Port, Stainless Steel Trim

The NIBCO® ball valve provides ease of operation with quarter-turn (90 degrees) open to close. The reinforced PTFE seat ring and stainless steel ball/stem exhibit high chemical resistance properties and is recommended for process piping. This valve features threaded ends for easy installation. Please refer to NIBCO technical data sheets, valve selection guides, chemical resistance guide and catalog for engineering and installation information. Choose NIBCO® ball valves for the most specified,

[+ more](#)



Specifications

| | |
|------------------------|-------------------------------|
| UPC Code | 039923793249 |
| Type | Ball Valve |
| Valve Size | 1 1/2 |
| Connection Type | T -- Female NPT Thread (FIPT) |
| Seal Material | RPTFE (Reinforced) |
| Seat Material | RPTFE (Reinforced) |
| Stem Material | SS - Stainless Steel |
| Ball Material | SS - Stainless Steel |
| Body Material | Stainless Steel |
| Cv Coefficient | 64 |

| | |
|------------------------------|---|
| Valve Operator | CS Locking Lever Handle |
| Description | T580S6R66LL 1 1/2 THRD BALL LKG LEV 2PC S |
| eClass Classification | Stainless Steel Ball Valves |
| Turns/Operation | Quarter-Turn |
| Weight | 3.760 lb |