

SUBMITTAL DATA

JOB/CUSTOMER:

SUBMITTED BY:


ENGINEER:

APPROVED BY:

CONTRACTOR:

ORDER NO:


SPECIFICATION REF:



NOMENCLATURE

S Stainless
3 3-Speed
100 Series


MOUNTING POSITIONS



TECHNICAL DATA

FLOW RANGE 0-25 GPM**HEAD RANGE** 0-18 feet**MOTORS** 2-Pole Single Phase**MIN. FLUID TEMPERATURE** 36° F**MAX. FLUID TEMPERATURE** 230° F**MAX. WORKING PRESSURE** 145 PSI.**CONNECTORS** GF 15/26 Flange
(with 3/4" Stainless Steel MIP shown in picture)**HP MAX SPEED** .116 hp**VOLTAGE (max. spd.)** 115v/ 87 watts/ .75 Amps**APPROX. SHIP WEIGHT** 9 LBS

DIMENSIONS



* Dimensions shown do not include connectors

PERFORMANCE CHART

