

# T220 / GL220 SERIES ANSI A156.5 GRADE 3 STANDARD DUTY DEADBOLTS / GATE LATCHES


Available with Interchangeable Core for Best, Falcon & Arrow


Available with Interchangeable Core for Schlage Full Size Format OEM Cylinders

## T220 STANDARD DUTY DEADBOLTS GL220 STANDARD DUTY GATE LATCHES

FOR LIGHT COMMERCIAL AND RESIDENTIAL APPLICATIONS







#### **SPECIFICATIONS**

#### TRIM

Wrought Brass or Stainless Steel.

#### **DOOR RANGES**

Adjustable 1 3/8" (35mm) to 1 3/4" (45mm) door thickness.

#### **BACKSET**

Adjustable 2 %" or 2 3/4" for T220 and T330. For GL220 and GL330 specify backset.

#### **DEADBOLT FACEPLATE**

Standard 2  $\frac{1}{4}$ " X 1" packed with  $\frac{1}{8}$ " plastic filler to convert 1" face plate to 1  $\frac{1}{8}$ " wide door preparations.

#### **BORE DIAMETER**

1" for latch, 1 ½" or 2 1/8" for lock housing.

#### **STRIKE**

1 1/8" X 2 3/4" square corner.

#### **CYLINDER & KEYWAYS**

6 pin solid brass "C" keyway standard.

#### **● INTERCHANGEABLE CORE**

Interchangeable Core locks will accept compatible 6 or 7 pin cores with BEST, FALCON and ARROW.

Interchangeable Core locks will also accept SCHLAGE full size format OEM interchangeable core cylinders and compatible Schlage 6-Pin Interchangeable Core. Interchangeable Core offered by Cal-Royal Products Inc.


### T220/GL220 SERIES FINISHES AND FUNCTIONS



FINISHES AVAILABLE		
BHMA SYMBOL	US CODE	DESCRIPTION
605	US3	Polished Brass
606	US4	Satin Brass
609	US5	Antique Brass
612	US10	Satin Bronze
613	US10B	Oil Rubbed Bronze
619	US15	Satin Nickel
625	US26	Polished Chrome
626	US26D	Satin Chrome

#### Refer to price list for stock finishes and functions







T220 SICT220 SCICT220 ANSI E0153



#### Single Cylinder Deadbolt

Dead locking latch bolt retracted by key from outside or by thumb turn on inside. Adjustable 2 % or 2 % backset.





Dead locking latch bolt retracted by key from either side. Otherwise always locked. (2 %" backset)





#### **Double Cylinder Deadbolt**

Dead locking deadbolt retracted by key from either side. Adjustable 2 % or 2 % backset.





#### **Double Cylinder Gate Latch**

Dead locking latch bolt retracted by key from either side. Otherwise always locked. (2 ¾" backset)

**ID58** 



**One Sided Dead Bolt** 

Deadbolt thrown or retracted by turn unit only. No outside trim. Bore halfway through door for installation visible from one side of door only.





#### One Sided Latch Bolt

Dead latch retracted by thumb turn, no outside trim. Visible from one side of door only. Otherwise always locked.

ID60



**One Sided Dead Bolt** 

Deadbolt thrown or retracted by turn unit only. Blank plate is on external trim to be used on bore holes 1 %" and 2 %" wide.

GL60



#### **One Sided Latch Bolt**

Dead latch retracted by thumb turn unit. Blank plate on external trim to be used on bore holes 1 %" and 2 %" diameter. Otherwise always locked.

GL220 ICGL220 ANSI F0153



**Single Cylinder Gate Latch** 

Dead locking latch bolt retracted by key from outside or by thumb turn on inside. Otherwise always locked (2 %" backset)

GL58234



#### **One Sided Latch Bolt**

Dead latch retracted by thumb turn, no outside trim. Visible from one side of door only. Otherwise always locked.

GL220234 ICGL220234 ANSI E0142



**Single Cylinder Gate Latch** 

Dead locking latch bolt retracted by key from outside or by thumb turn on inside. Otherwise always locked. (2 ¾" backset)



#### One Sided Latch Bolt

Dead latch retracted by turn unit. Blank plate on external trim to be used on bore holes 1 %" and 2 %" diameter. Otherwise always locked.



ADDITIONAL PARTS		
GL238	2 ¾" dead latch (1 ¼" x 2 ¼")	
GL234	2 ¾" dead latch (1 ½" x 2 ½")	

"IC" Indicates function available with BEST, FALCON & ARROW Interchangeable Core.

"SCIC" Indicates function available with SCHLAGE full size format Interchangeable Core.

HOLD BACK FEATURE ON DEADBOLT WITH GATE LATCH NOT AVAILABLE OTHER FUNCTIONS NOT LISTED AVAILABLE UPON REQUEST





6605 Flotilla St., Commerce, CA 90040 U.S.A.

Tel: (323) 888-6601 ◆ Fax: (323) 888-6699

Website: www.cal-royal.com ◆ Email: sales@cal-royal.com