



800 SERIES ANSI GRADE 3 STANDARD DUTY CYLINDRICAL LEVERSETS

EPIC


Meets ADA requirements
Specially designed for
Barrier Free Application
Conforms with ANSI A156.2
Series 4000, Grade-3
Exceeds 200,000 cycles

Push in button
function

STANDARD DUTY CYLINDRICAL LEVERSET
MEETS ANSI STANDARD A156.2, GRADE 3

Cylindrical Body


3 ¾" length lever handle with ½" return



Guard bolt deadlocks latch bolt automatically

Throw bolt affords a high degree of security

mounting
Latch case sturdy, all
steel mechanism



Solid brass 5 pin "C" keyway cylinder

Threaded rose conceals

SPECIFICATIONS

APPLICATIONS

For residential or light commercial applications.

DOOR RANGES

1 3/8" to 2" thickness doors.

BACKSET

2 %" or 2 ¾" backset.

LATCHBOLT

Die-Cast Zinc, Brass, Chrome or Brass plated $^{7}/_{16}$ " (11mm) Throw Latch Bolt.

LATCH FACEPLATE

2 1/4" x 1 1/8" for 2 3/4" backset. 2 1/4" x 1" for 2 3/4" backset.

EXPOSED TRIM

Concealed screw

Wrought brass, bronze or stainless steel, levers are Zinc casting, plated to match trim finish.

STRIKES

Optional "T", full lip or ASA strike.

ANSI STANDARDS

Meets or exceeds requirements of BHMA/ANSI A156.2 Series 4000, Grade 3.

CYLINDER & KEYWAYS

5 pin solid brass Schlage "C" keyway standard.

LATCH & STRIKE SCREWS


8-32 x 1"FPH Dual Purpose.

EPIC 800 SERIES FINISHES AND FUNCTIONS



FINISHES AVAILABLE		
BHMA SYMBOL	US CODE	DESCRIPTION
605	US3	Polished Brass
606	US4	Satin Brass
609	US5	Antique Brass
612	US10	Satin Bronze
613	US10B	Oil Rubbed Bronze
619	US15	Satin Nickel
625	US26	Polished Chrome
626	US26D	Satin Chrome

DOOR PREPARATION



Refer to price list for stock finishes and functions

800 ANSI: F82



ENTRANCE PUSH BUTTON

Push button locking. Pushing button locks outside lever requiring use of key until button is manually unlocked. Pushing button locks outside lever until unlocked with key or inside lever is turned.

802 ANSI: F76



PRIVACY

Latch bolt operated by lever from either side. Outside lever is locked by push button inside and unlocked by emergency release outside. **Turning inside lever or closing door releases push button.**

803 ANSI: F75



PASSAGE

Latch bolt operated by lever from either side at all times

805



DUMMY LEVER

Single dummy trim for one side of door. Pull only.

OTHER FUNCTIONS NOT LISTED AVAILABLE UPON REQUEST



