

D460041



D460041

SPECIFICATIONS

TOPANGA™ 3 1/2" SHOWERHEAD

Model

D460041

Description

- Pressure Manifold™ & Air Injection Technology
- Brass ball joint with polymer shell
- Optimizes water intensity even at low pressures
- With 40 easy clean jets
- Uses 40% less water than a standard showerhead flowing at 2.5 gpm
- Maximum flow rate 1.5 gpm @ 80 psi

Standards



• UPC/cUPC

• Energy policy act of 1992


MEETS ASME
A112.18.1M / A112.18.1

• ASME A112.18.1M/A112.18.1

Warranty


Danze products are covered by a manufacturer's limited "lifetime" warranty for manufacturing defects.

Flow Rate



Finishes Available

- Chrome
- Other: Refer to Price List for additional finish



Submittal Information:

Job Name: _____

Location: _____

Contractor: _____

Contact #: _____