




## HTWP1400F– Hotpoint® 3.5 DOE cu. ft. capacity washer

### Washer Dimensions (in inches)



**Circuit Requirements:** An individual, properly-grounded branch circuit, with a three-prong grounding-type receptacle, protected by a 15 or 20 amp circuit breaker or a time-delay fuse, is required.


**Electrical Rating:** 115V, 60Hz, 10 Amps

**Installation Information:** Before installing, consult installation instructions packed with product for current dimensional data.

**Washer Note:** Washer wall outlet must be located within 36" of service cord entry. Wall outlet must not be located behind dryer.



## HTWP1400F– Hotpoint® 3.7 DOE cu. ft. capacity washer



### Features and Benefits

- Plastic ribbed basket - Removes more moisture than smooth baskets
- Auto balance suspension system - Handles the heaviest loads without banging or walking
- Dual-Action Agitator - Provides gentle, dual-wash action
- Power Rinse option - Optional deep-rinse cycle ensures clothes are rinsed of soap residue and fabric softener
- 4 water levels - Select water level based on load size
- 8 wash cycles - Handle various fabrics and soils
- 3 wash/rinse temperatures - A variety of temperatures provide great wash results
- Model HTWP1400FWW – White