



SUBMITTAL INFORMATION

70 Series Coppersetter - (VHH77-xx-11-77-NL style)



ANGLE KEY VALVE BY ANGLE DUAL CHECK VALVE (2" METER)

FEMALE IRON PIPE THREAD INLET AND OUTLET



SERVICE LINE CONNECTION		HEIGHT	APPROX. WT. LBS.	CATALOG NUMBER	✓ SUBMITTED ITEM(S)
FIP INLET	FIP OUTLET				
2"	2"	12"	32	VHH77-12-11-77-NL	
		15"	33	VHH77-15-11-77-NL	
		18"	34	VHH77-18-11-77-NL	
		21"	34	VHH77-21-11-77-NL	
		24"	35	VHH77-24-11-77-NL	
		27"	35	VHH77-27-11-77-NL	

FEATURES

- All brass components that come in contact with potable water conform to AWWA Standard C800 (UNS NO C89833)
- The product has the letters "NL" cast into the main body for proper identification
- Brass components that do not come in contact with potable water conform to AWWA Standard C800 (ASTM B-62 and ASTM B-584, UNS NO C83600 - 85-5-5-5)
- Constructed with Type K Copper and conforms to ASTM B-88, Copper Alloy #122
- All Ford Meter Setters are assembled with lead-free solder
- Bracing Eyes are standard
- Meter Support Brackets are standard
- Optional Bottom bar Bypass - add "B" following the height. Example: VH77-12B-11-77-NL
- Optional High Bypass - add "HB" following the height. Example: VH77-12HB-11-77-NL
- Padlock wing is standard on all Angle Meter Ball Valves or Key Valves

The Ford Meter Box Company considers the information in this submittal form to be correct at the time of publication. Item and option availability, including specifications, are subject to change without notice. Please verify that your product information is current.



The Ford Meter Box Company, Inc.

P.O. Box 443, Wabash, Indiana U.S.A. 46992-0443

Phone: 260-563-3171 / Fax: 800-826-3487

Overseas Fax: 260-563-0167

<http://www.fordmeterbox.com>

01/02/14

Submitted By: