For Residential and Commercial Applications						
Job Name		Engineer / Architect				
Job Location		Wholesaler				
Submittal Date		Contractor				

Use: For use in potable water distribution systems in accessible locations only. Not intended for recirculating water systems that produce continuous use temperatures above 115° F. For those applications, use our KTTM series ball stop supply kits.

Design Features:

- **Everything you need.** These kits combine our trusted BrassCraft® supply stop, copper riser, and escutcheon for an easy-to-install connection
- No Lead

Copper Riser Provides:

- One-piece construction
- Cut-to-length for a clean, professional installation

Multi-Turn Stop Provides:


- Machined one-piece brass body provides strength, durability, and long-lasting performance
- Oval knurled handle provides a secure grip and smooth on/off operation
- Easy-to-remove handle helps protect against accidental stop operation during rough-ins

Operating Specifications:

Temperature: 40°-140° F

Pressure: 125 PSI maximum

Tubing Diameter: 3/8" OD



RISER MATERIAL SPECIFICATIONS				
Tube	Copper or copper, chrome plated			
Insert	POM			


STOP MATERIAL SPECIFICATIONS				
Body	Brass or brass, plated			
Stem	POM; brass; or brass, plated			
Handle	Zinc, die cast plated; ABS, plated; or Polycarbonate			
Handle Screw	Steel, plated			
Bib & Packing Washer	Rubber			
Packing Nut	Brass or brass, plated			
Loose Key	Zinc, die cast			
Loose Key Stem	Brass, plated			
Lock Shield	Brass or brass, chrome plated			




Part Listing: OCR1912AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 11-1/2" length riser & shallow escutcheon, chrome plated OCR1912AX R 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 11-1/2" length riser & shallow escutcheon, rough brass OCR1912AZX C 1/2" nom compression x 3/8" OD compression stop, brass stem with 3/8" OD tube x 11-1/2" length riser & shallow escutcheon, chrome plated OCR1915AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 14-1/2" length riser & shallow escutcheon, chrome plated OCR1920AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 19-1/2" length riser & shallow escutcheon, chrome plated OCR1920AX BZ 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 19-1/2" length riser & shallow escutcheon, oil rubbed bronze 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 19-1/2" OCR1920AX NS length riser & shallow escutcheon, satin nickel OCR1920AZX C 1/2" nom compression x 3/8" OD compression stop, brass stem with 3/8" OD tube x 19-1/2" length riser & shallow escutcheon, chrome plated OCR1920AZX R 1/2" nom compression x 3/8" OD compression stop, brass stem with 3/8" OD tube x 19-1/2" length riser & shallow escutcheon, rough brass SCR1912AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 11-1/2" length riser & shallow escutcheon, loose key, chrome plated SCR1915AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 14-1/2" length riser & shallow escutcheon, loose key, chrome plated 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 19-1/2" SCR1920AX C length riser & shallow escutcheon, loose key, chrome plated SSCR1912AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 11-1/2" length riser & shallow escutcheon, screwdriver slot, chrome plated 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 14-1/2" SSCR1915AX C length riser & shallow escutcheon, screwdriver slot, chrome plated 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 19-1/2" SSCR1920AX C length riser & shallow escutcheon, screwdriver slot, chrome plated 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 11-1/2" STCR1912AX C length riser & shallow escutcheon, loose key, stuffing box, lock shield, chrome plated STCR1915AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 14-1/2" length riser & shallow escutcheon, loose key, stuffing box, lock shield, chrome plated STCR1920AX C 1/2" nom compression x 3/8" OD compression stop with 3/8" OD tube x 19-1/2" length riser & shallow escutcheon, loose key, stuffing box, lock shield, chrome plated



PART DIMENSIONS (Inches)							
Model	DIM. A	DIM. B	DIM. C	DIM. D	DIM. E	DIM. F	
OCR1912AX /AZX	12.0	1.16	2.84	13.0	-	1.14	
OCR1915AX	15.0	1.16	2.84	16.0	1	1.14	
OCR1920AX /AZX	20.0	1.16	2.84	21.0	1	1.14	
SCR1912AX	12.0	1.20	2.64	13.0	4.49	.88	
SCR1915AX	15.0	1.20	2.64	16.0	4.49	.88	
SCR1920AX	20.0	1.20	2.64	21.0	4.49	.88	
SSCR1912AX	12.0	1.20	2.64	-	-	.88	
SSCR1915AX	15.0	1.20	2.64	-	-	.88	
SSCR1920AX	20.0	1.20	2.64	-	-	.88	
STCR1912AX	12.0	1.20	3.03	13.0	4.88	.88	
STCR1915AX	15.0	1.20	3.03	16.0	4.88	.88	
STCR1920AX	20.0	1.20	3.03	21.0	4.88	.88	







Listings & Certifications:

- IAPMO listed to ASME A112.18.1 / CSA B125.1 (Including NSF 61 and NSF 372)(File 0645)
- CSA listed to ASME A112.18.1 / CSA B125.1 (Including NSF 61 and NSF 372)(File 204593)
- No-lead product CSA listed to NSF 372 (Class 6853-01)









