Key Machine

045 HD

Manual Duplicator



PERFORMANCE Series


Accurate, economical, and easy to use, the 045 HD is the perfect basic duplicator for virtually any store or shop. Wide vise jaw spacing, Super Jaw 3, “secure grip” vise jaws, dial type depth adjustment, and simple operation are just a few reasons that the 045 is the manual style duplicator of choice for so many!

The ilco to your success

ilco A member of the Kaba Group
www.kaba-ilco.com

045 HD Manual Duplicator

A real money-maker, the 045 is the perfect basic key duplicator, ideal for virtually any key cutting outlet. Economical, accurate, and simple to operate, the 045 HD is loaded with useful features any user will readily appreciate. Its performance tested design makes it an excellent choice for store, shop or mobile use. Performance tested to assure years of dependable service.



- **Super Jaw 3, "secure grip", four-position vise jaws; securely clamps most residential, padlock, or automotive keys without the need for adapters, including double-sided types.**
- **Permanently lubricated cutter spindle shaft ball bearings rather than bushings; bearings are usually found on more expensive models.**
- **Hardened carriage shaft and cutter spindle provide extended service life.**
- **Wide spacing between vise jaws; accommodates longer key types.**
- **Dial type depth adjustment system greatly simplifies calibration and improves accuracy.**
- **Ideal for shop or mobile use; efficient 1/4 HP motor will operate with most inverters and generators that supply 500 watts (continuous) or higher output (115 Volt AC).**
- **Special depth limit device guards against cutter contact with vise jaws.**
- **Features a "soft-touch" deburring brush.**
- **Cutter is made of high speed tool steel, coated with titanium nitride for longer cutting life.**
- **Built in circuit breaker protection.**

Specifications:

Motor:	110V-AC standard; also 220V; all 1/4 hp, 1725 rpm
Vise Jaws:	Super Jaw 3, four-position
Cutter:	P-X23MC; titanium coated
Brush:	814-00-51
Dimensions:	14 1/2"W x 17 1/2" D x 8 3/4"H (36.8cm x 44.5cm x 22.2cm)
Weight:	26.1 lbs. (11.85 kg)

Meets OSHA and CSA/NRTL/C* requirements.
** Applies to 110 Volt model only*

Duplicates Cylinder and Automotive Keys



The Ilco to your success

Kaba Ilco Corp.
400 Jeffreys Road · Rocky Mount, NC 27804
Phone **800.334.1381** · Fax **252.446.4702**
www.kaba-ilco.com

Form # 2980/0709