5MR16/LED /40' /3000K /120V /GU10 /DIM
5 Watt; MR16; 3000K; 40' Beam Spread; Gu10 Base; 120 Volts

Features
- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

View Dimmer Compatibility



S9008

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9008	045923090080	5	MR16	GU10	GU10	5MR16/LED /40' /3000K /120V /GU10 /DIM	120

MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	CRI	Pack	Package Type
2.25"	2.00"	370	25000	3000	80	12	CD/1

Beam Spread	RoHS Compliant	UL or ETL Listed
40	Yes	Yes

National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051