ID Infinity Drain




FXAS 65 Series Fixed Length

- FXAS 6532 32" Complete Kit
- FXAS 6536 36" Complete Kit
- FXAS 6542 42" Complete Kit
- FXAS 6548 48" Complete Kit
- FXAS 6560 60" Complete Kit

Features

- Pre-pitched channel with fixed lengths and fixed center outlet
- Indoor or outdoor use
- 16 gauge, 304L Stainless steel channel
- 12 gauge, 316L stainless steel Wedge Wire grate
- Works with 2" clamp down floor drain with 2" throat/strainer size (NOT included)
- Compatible with: PVC Liner, Rubber Liner (Chloraloy ®), Hot Mop, Lead Pan, Copper Pan, or Fiberglass
- Grate can be removed completely for cleaning
- Flow rate 9 gpm per outlet
 - Flow rate measured at outlet only. Measurement does not account for water in channel or sheeting on shower floor.



Care & Maintenance

FXAS 65 stainless steel linear drain top grates are made of 316L stainless steel. This material is non-porous, hygienic, rust-free and extremely durable. Bar Keepers Friend® and Soft Scrub® are commonly available products that can be used to protect and clean your Satin Stainless drain cover. For stains that have been left for an excessive amount of time, stronger cleaning agents such as Steel Brite® may be needed. For Polished Stainless and Oil Rubbed Bronze we recommend a mild soap and a soft cloth for cleaning. DO NOT use any abrasive cleaners, scrub pads or allow household cleaning agents, such as bleach, to sit on the drain cover for a long period of time. Stainless steel does not rust. External factors, such as contamination from other highly ferrous metals, built up road salt, sea salt, or chlorine may have caused "surface" rust which can be removed using Barkeepers Friend®, Soft Scrub® with Bleach, or Steel Brite®. Always follow the directions on the bottle. Follow proper maintenance procedures to prevent excessive surface rust. In areas of frequent exposure to salt, chlorine, and other chemical compounds, maintenance of the stainless grates should be performed at least 2-3 times per year.


Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.lnfinitydrain.com






NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.

ID Infinity Drain





Model Number	Complete Kit Contents	A (Maximum Overall Length)	B (Maximum Grate Length)
FXAS 6532	1 - WA 6532 Grate 1 - XC 6532 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	32 1/8″	31 7/8"
FXAS 6536	1 - WA 6536 Grate 1 - XC 6536 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	36 1/8"	35 7/8"
FXAS 6542	1 - WA 6542 Grate 1 - XC 6542 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	42 1/8"	41 7/8"
FXAS 6548	1 - WA 6548 Grate 1 - XC 6548 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	48 1/8"	47 7/8"
FXAS 6560	1 - WA 6560 Grate 1 - XC 6560 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	60 1/8"	59 7/8"

Stock Finishes					
□ Satin Stainless	□ Polished Stainless	□ Satin Bronze	□ Matte Black	□ Matte White	

Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com





NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.



	OPTIONAL COMPONENTS					
TNAS - 2	2" Long Threaded Nipple					
TNAS - 3	3" Long Threaded Nipple					
TNAS - 4	4" Long Threaded Nipple					
TNRN -S	Stainless Steel Extension Nipple					
TNRN-P	TNRN-P PVC Extension Nipple					
UCP 2	Universal 2" Clamping Plate					
UCP 42	UCP 42 Universal Reducing Plate (Adapts 4" or 3" existing throat size to 2")					
CDI 22	CDI 22 Clamp Down Drain, Cast Iron, 2" Throat, 2" No Hub Outlet					
CDA 22	CDA 22 Clamp Down Drain, ABS, 2" Throat, 2" No Hub Outlet					
CDP 22	CDP 22 Clamp Down Drain, PVC, 2" Throat, 2" No Hub Outlet					
CDIT 22	CDIT 22 Clamp Down Drain, Cast Iron, 2" Throat, 2" Threaded Outlet					
CDIC 22	Clamp Down Drain, Cast Iron, 2" Throat, 2" Inside Caulk Outlet					
CDIS 22	Clamp Down Drain, Cast Iron, Integral Trap 2" Throat, 2" Threaded Side Outlet					
CDIQ 42	CDIQ 42 Clamp Down Drain, Cast Iron, Side Outlet No Trap 4" Throat, 2" Outlet (For use with UCP 42)					
Custom Finishes	Y2 Y1 Y2 Y3					
□ Satin Stainless	□ Polished Stainless □ Oil Rubbed Bronze □ Matte Black □ Matte White □ Satin Bronze					
NOTE: Custom color matching available upon request						
Desired finished For lengths great Y: OUTLET LOC	verall Length of Channel (inches): dimension er than 60", multiple grates are supplied, unless otherwise noted. CATION: # of outlets Center of Outlet(s) to right edge: Y1 Y2 Y3 NO lied per set-up. Turnaround is 5 business days, plus shipping. (Rush does not apply to some custom designs, please contact Infinity Drain for details)					

Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com

Customer: _

Approved by: ___





NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.

Job Name: __

Date: _