### ID Infinity Drain




# FXED 65 Series FIXED LENGTH

- FXED 6532 32" Complete Kit
- FXED 6536 36" Complete Kit
- FXED 6542 42" Complete Kit
- FXED 6548 48" Complete Kit
- FXED 6560 60" Complete Kit

#### **Features**

- Pre-pitched channel with "Fixed" lengths and "Fixed" center outlets
- Indoor or outdoor use
- Stainless steel channel
- 16 gauge, 304L stainless steel grate and channel
- Works with 2" clamp down floor with 2" throat/strainer size (not included)
- Compatible with: PVC Liner, Rubber Liner (Chloraloy ®), Hot Mop, Lead Pan, Copper Pan, or Fiberglass
- Grate can be removed completely for cleaning
- Flow rate 9 gpm per outlet
  - Flow rate measured at outlet only. Measurement does not account for water in channel or sheeting on shower floor.



#### Care & Maintenance

FXED 65 stainless steel linear drain top grates are made of 304L stainless steel. This material is non-porous, hygienic, rust-free and extremely durable. Bar Keepers Friend® and Soft Scrub® are commonly available products that can be used to protect and clean your Satin Stainless drain cover. For stains that have been left for an excessive amount of time, stronger cleaning agents such as Steel Brite® may be needed. For Polished Stainless and other finishes we recommend a mild soap and a soft cloth for cleaning. DO NOT use any abrasive cleaners, scrub pads or allow household cleaning agents, such as bleach, to sit on the drain cover for a long period of time. Stainless steel does not rust. External factors, such as contamination from other highly ferrous metals, built up road salt, sea salt, or chlorine may have caused "surface" rust which can be removed using Barkeepers Friend®, Soft Scrub® with Bleach, or Steel Brite®. Always follow the directions on the bottle. Follow proper maintenance procedures to prevent excessive surface rust. In areas of frequent exposure to salt, chlorine, and other chemical compounds, maintenance of the stainless grates should be performed at least 2-3 times per year.


Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com





NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.

## ID Infinity Drain



Model Number	Complete Kit Contents	A (Maximum Overall Length)	B (Maximum Grate Length)	
FXED 6532	1 - EA 6532 Stainless Steel Grate 1 - XC 6532 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 2" Hair Strainer 1 - AKEY Lift Out Key	32 1/8″	31 7/8"	
FXED 6536	1 - EA 6536 Stainless Steel Grate 1 - XC 6536 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 2" Hair Strainer 1 - AKEY Lift Out Key	36 1/8″	35 7/8"	
FXED 6542	1 - EA 6542 Stainless Steel Grate 1 - XC 6542 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 2" Hair Strainer 1 - AKEY Lift Out Key	42 1/8"	41 7/8"	
FXED 6548	1 - EA 6548 Stainless Steel Grate 1 - XC 6548 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 2" Hair Strainer 1 - AKEY Lift Out Key	48 1/8"	47 7/8"	
FXED 6560	1 - EA 6560 Stainless Steel Grate 1 - XC 6560 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 2" Hair Strainer 1 - AKEY Lift Out Key	60 1/8"	59 7/8"	

Stock Finishes		
□ Satin Stainless	□ Polished Stainless	□ Oil Rubbed Bronze

Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com





NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.



OPTIONAL COMPONENTS					
TNAS - 2	2" Long Threaded Nipple				
TNAS - 3	3" Long Threaded Nipple				
TNAS - 4	4" Long Threaded Nipple				
TNRN -S	Stainless Steel Extension Nipple				
TNRN-P	PVC Extension Nipple				
UCP 2	Universal 2" Clamping Plate				
UCP 42	Universal Reducing Plate (Adapts 4" or 3" existing throat size to 2")				
CDI 22	Clamp Down Drain, Cast Iron, 2" Throat, 2" No Hub Outlet				
CDA 22	Clamp Down Drain, ABS, 2" Throat, 2" No Hub Outlet				
CDP 22	Clamp Down Drain, PVC, 2" Throat, 2" No Hub Outlet				
CDIT 22	Clamp Down Drain, Cast Iron, 2" Throat, 2" Threaded Outlet				
CDIC 22	Clamp Down Drain, Cast Iron, 2" Throat, 2" Inside Caulk Outlet				
CDIS 22	Clamp Down Drain, Cast Iron, Integral Trap 2" Throat, 2" Threaded Side Outlet				
CDIQ 42	Clamp Down Drain, Cast Iron, Side Outlet No Trap 4" Throat, 2" Outlet (For use with UCP 42)				
□ FXED 65 CUSTOM					

Custom Finishes					
□ Satin Stainless	<ul><li>Polished Stainless</li></ul>	□ Oil Rubbed Bronze	□ Matte Black	□ Matte White	□ Satin Bronze
NOTE: Custom color	matching available upon request				

For lengths greater than 60", multiple grates are supplied, unless otherwise noted.
Y: OUTLET LOCATION: # of outlets   Center of Outlet(s) to right edge: Y1 Y2 Y3
RUSH: Yes NO Rush charge applied per set-up. Turnaround is 5 business days, plus shipping, (Rush does not apply to some custom designs, please contact Infinity Drain for details)

Approved by: \_\_\_\_\_ Date: \_\_\_\_\_

Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com

Customer: \_\_\_

Desired finished dimension



X: LENGTH: Overall Length of Channel (inches):



NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.

Job Name: \_\_\_\_\_