### ID Infinity Drain




# FXTIF 65 Series

- FXTIF 6520 20" Complete Kit
- FXTIF 6540 40" Complete Kit
- FXTIF 6548 48" Complete Kit
- FXTIF 6560 60" Complete Kit

#### Features

- Pre-pitched channel with fixed lengths and fixed center outlet
- Indoor or outdoor use
- 16 gauge, 304L stainless steel channel
- 12 gauge, 304L stainless steel Tile Insert Frame
- Works with 2" clamp down floor with 2" throat/strainer size (NOT included)
- Compatible with: PVC Liner, Rubber Liner (Chloraloy ®), Hot Mop, Lead Pan, Copper Pan, or Fiberglass
- Grate can be removed completely for cleaning
- Flow rate 9 gpm per outlet
  - Flow rate measured at outlet only. Measurement does not account for water in channel or sheeting on shower floor.




#### Care & Maintenance

FXTIF 65 stainless steel linear drain top grates are made of 304L stainless steel. This material is non-porous, hygienic, rust-free and extremely durable. Bar Keepers Friend® and Soft Scrub® are commonly available products that can be used to protect and clean your Satin Stainless drain cover. For stains that have been left for an excessive amount of time, stronger cleaning agents such as Steel Brite® may be needed. For Polished Stainless and other finishes we recommend a mild soap and a soft cloth for cleaning. DO NOT use any abrasive cleaners, scrub pads or allow household cleaning agents, such as bleach, to sit on the drain cover for a long period of time. Stainless steel does not rust. External factors, such as contamination from other highly ferrous metals, built up road salt, sea salt, or chlorine may have caused "surface" rust which can be removed using Barkeepers Friend®, Soft Scrub® with Bleach, or Steel Brite®. Always follow the directions on the bottle. Follow proper maintenance procedures to prevent excessive surface rust. In areas of frequent exposure to salt, chlorine, and other chemical compounds, maintenance of the stainless grates should be performed at least 2-3 times per year.


Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com






NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.

## ID Infinity Drain





2 INCH CLAMP DOWN ASSEMBLY NOT INCLUDED IN KIT SKU (MATERIAL CAN BE CAST IRON, ABS, OR PVC)

Model Number	Complete Kit Contents	A (Maximum Overall Length)	<b>B</b> (Maximum Grate Length)
FXTIF 6520	1 - TA 6520 Tile Insert Frame 1 - IC 6520 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	20 1/8″	19 7/8″
FXTIF 6540	1 - TA 6540 Tile Insert Frame 1 - IC 6540 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	40 1/8"	39 7/8″
FXTIF 6548	1 - TA 6548 Tile Insert Frame 1 - IC 6548 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	48 1/8″	47 7/8″
FXTIF 6560	1 - TA 6560 Tile Insert Frame 1 - IC 6560 Fixed Channel 1 - TNAS Threaded Nipple 1 - HS 2 Hair Strainer 1 - AKEY Lift Out Key	60 1/8"	59 7/8"

#### **Stock Finishes**

Satin Stainless (SS)

Polished Stainless (PS)

🗆 Satin Bronze (SB)

Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com






NOTE: Installer must verify all rough-in dimensions prior to installation and consult local and national codes. Conformity and compliance to local and national codes are the responsibility of the installer.

### ID Infinity Drain

OPTIONAL COMPONENTS						
TNAS - 2	NAS - 2 2" Long Threaded Nipple					
TNAS - 3	3" Long Threaded Nipple					
TNAS - 4	4" Long Threaded Nipple					
TNRN -S	Stainless Steel Extension Nipple					
TNRN-P	PVC Extension Nipple					
UCP 2	Universal 2" Clamping Plate					
UCP 42	Universal Reducing Plate (Adapts 4" or 3" existing throat size to 2")					
CDI 22	Clamp Down Drain, Cast Iron, 2" Throat, 2" No Hub Outlet					
CDA 22	Clamp Down Drain, ABS, 2" Throat, 2" No Hub Outlet					
CDP 22	Clamp Down Drain, PVC, 2" Throat, 2" No Hub Outlet					
CDIT 22	Clamp Down Drain, Cast Iron, 2" Throat, 2" Threaded Outlet					
CDIC 22	Clamp Down Drain, Cast Iron, 2" Throat, 2" Inside Caulk Outlet					
CDIS 22	Clamp Down Drain, Cast Iron, Integral Trap 2" Throat, 2" Threaded Side Outlet					
CDIQ 42	Clamp Down Drain, Cast Iron, Side Outlet No Trap 4" Throat, 2" Outlet (For use with UCP 42)					
EXTIE 65 CUSTOM						



		Y2	Y		
Custom Finishes					
🗆 Satin Stainless	Polished Stainless	🗆 Oil Rubbed Bronze	🗆 Matte Black	🗆 Matte White	🗆 Satin Bronze
NOTE: Custom color	r matching available upon request				
Desired finished dim	all Length of Channel (inches): nension han 60", multiple grates are supplied, un				
Y: OUTLET LOCAT	ION:# of outlets   Cer	nter of Outlet(s) to right edge	: Y1 Y2	Y3	
RUSH: Yes Rush charge applied	NO per set-up. Turnaround is 5 business day	/s, plus shipping. (Rush does not apply	to some custom designs	, please contact Infinity Drain fc	or details)
Customer:			Job N	ame:	
Approved by:		_	Date:		
Infinity Drain 145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.lnfinitydrain.com	MADE IN THE USA	ID Infinity Light Duty		dimensions prior to local and national cod	st verify all rough-in installation and consult les. Conformity and com- national codes are the staller.

145 Dixon Avenue Amityville, NY 11701 Phone: 516.767.6786 Fax: 516.740.3066 www.Infinitydrain.com



Dimensions are subject to manufacturer's tolerance and change without notice. We can assume no responsibility for use of superceded or void