

DRIVEN TO OUTPERFORM.



750 Es MAX FASTENING TORQUE

UP TO
1200 [Is NUT-BUSTING TORQUE

UP TO

2X

MORE
BUN-TIME

TORQUE

UP TO
1200
ILS
NUT-BUSTING
TORQUE

2X MORE RUN-TIME





M18 FUEL [™] 2764-22 vs COMPETITORS					
	Milwaukee®	Milwaukee®	Dewalt	Dewalt	
		**	7		
	2764-22	2664-22	DW294	DW297	
Motor	POWERSTATE™ Brushless	4-Pole Neo	2-Pole Ferrite	2-Pole Ferrite	
Max Fastening Torque	750 ftlbs.	525 ftlbs.	345 ftlbs.	434 ftlbs.	
Nut-Busting Torque	1,200 ftlbs.	750 ftlbs.	345 ftlbs.	434 ftlbs.	
Length	9"	8-7/8"	11-1/4"	15-1/8"	
Drive-Control™	Yes	No	No	No	
LED Light	Yes	No	No	No	
Powered By	REDLITHIUM™ XC4.0	REDLITHIUM™	A/C Cord	A/C Cord	

PROPRIETARY 2-MODE DRIVE CONTROL™

2764	MODE 1	MODE 2
No Load Speed (RPM/IPM)	0 - 1,200 / 0 - 1,700	0 - 1,700 / 0 - 2,300
Max Fastening Torque	375 ftlbs.	750 ftlbs.





M18 FUEL" 3/4" High Torque Impact Wrench w/ Friction Ring (Tool-Only)

2764-20

Includes: 2764-20 M18 FUEL™ 3/4" High Torque Impact Wrench w/ Friction Ring



M18 FUEL** 3/4* High Torque Impact Wrench w/ Friction Ring (Kit - 2 Batteries) 2764-22

Includes: 2764-20 M18 FUEL™ 3/4" High Torque Impact Wrench w/ Friction Ring, (2) M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Packs, M12™ & M18™ Multi-Voltage Charger, and Carrying Case