Location:



7-200 TempControl 7 Series Specification Submittal



Coordinating Model Numbers		Specification				
☐ HTA-100	High temp audio/visual alarm system	TempControl thermostatic mixing valve made from lead				
☐ T-425-200	3" bimetal dial thermometer	free** metal components. Features serviceable integral check stops (see table 1 for flow rates).				
□ BV-200	Volume control shut off valve	Temperature control range: 70°F - 150°F (21.1°C - 65.6°C)				
□ SV-200	Solenoid valve	Approach temperature: 5°F (-15°C)				
☐ TF-200	Tee fitting					
☐ WHA-1	Water hammer arrestor					
		**According to US Senate bill S.3874, the term "lead free" is defined as follows: "not more than a weighted average of 0.25 percent lead when used with respect to the wetted surfaces of pipes, pipe fittings, plumbing fittings, and fixtures"				
		Compliance				
Configurations		ASME A112.18.1/CSA B125.1				
□ A	Valve and piping assembly	ASME A112.18.3/CSA B125.3 ASSE 1017				
□В	Valve and piping in cabinet	CA 116875 (AB 1953)				
□ BW	Valve and piping in cabinet with cold water bypass	NSF 61.9 US S.3874				
		Warranty				
		5 Years - for commercial installations.				
Note: Append appropriate suffix to model number.		Refer to www.symmons.com/warranty for complete warranty information.				


Table 1: Flow Rate - gpm (L/min)									
Valve Model	Min. Flow Rate*	Min. Flow Rate	Pressure Differential - psi (kPa)						
			5 psi (34 kPa)	10 psi (69 kPa)	20 psi (138 kPa)	25 psi (172 kPa)	30 psi (207 kPa)	45 psi (310 kPa)	
7-200	0.5 gpm (1.9 L/min)	5 gpm (19 L/min)	7 gpm (27 L/min)	12 gpm (46 L/min)	18 gpm (68 L/min)	21 gpm (80 L/min)	23 gpm (87 L/min)	27 gpm (102 L/min)	

^{*}Minimum flow rate when valve is installed at or near the hot water source with recirculated tempered water and continuously operating circulating pump.





7-200 TempControl 7 Series Specification Submittal

Dimensions



TempControl Valve Sizes								
Inlet	Outlet							
3/4"	3/4"							
Measurements								
7-200								
1/2", 13 mm								
1 7/8", 46 mm								
8 15/16", 226 mm								
5 15/16", 150 mm								
2", 51 mm								
3 5/16", 84 mm								
1 5/16", 33 mm								
11/16", 17 mm								
	Inlet 3/4" Measurement 7-2 1/2", 1 7/8", 8 15/16" 2", 5 3 5/16" 1 5/16"							





Note:

Dimensions are subject to change without notice.