

95ALF Series

Stop and Waste Ball Valve

LEAD FREE



Job Name:	
Job Location:	
Engineer:	
Contractor:	
Tag:	
PO#:	
Rep:	
Wholesale Dist.:	

DESCRIPTION

The Apollo International™ 95ALF Lead Free* Forged Brass Stop and Waste Ball Valve combines reliable operation with maximum economy. Ideal for plumbing or hydronic systems where draining is required. IAPMO listed and ANSI 3rd party certified lead free.

FEATURES

- Lead Free* Materials and Certification
- 2 Piece, Full-Port Design
- Blowout-Proof Stem Design
- Adjustable stem packing Nut
- Drain Port With Finger Tight Shut-Off
- Fast, Quarter-Turn Operation

APPROVALS

- IAPMO IGC 157
- NSF/ANSI 61 Water Quality
- NSF/ANSI 372 Lead Free

PERFORMANCE RATING

- Maximum Pressure: 600 psi CWP
- Temperature Range: 32°F - 250°F


STANDARD MATERIALS LIST

BODY	Lead Free Brass DZR
RETAINER	Lead Free Brass DZR
BALL	Lead Free Brass DZR, Chrome Plated
STEM	Lead Free Brass DZR
SEATS	PTFE
STEM PACKING	PTFE
GLAND NUT	Brass
O-RING	EPDM
HANDLE	Plated Steel w/ PVC Grip
WASHER	Plated Steel

****95ALF-2xx intended for soft solder installation using solders with melting temperature of < 500°F.**

DIMENSIONS

MODEL NUMBER	SIZE (IN.)	DIMENSIONS (IN.)				
		A	B	C	D	E
THREADED						
95ALF-103-01	1/2	0.59	2.24	1.78	3.74	-
95ALF-104-01	3/4	0.79	2.53	2.09	3.94	-
95ALF-105-01	1	0.98	3.15	2.36	4.33	-
SOLDER						
95ALF-203-01	1/2	0.59	2.12	1.78	3.74	0.63
95ALF-204-01	3/4	0.79	2.87	1.94	3.94	0.88
95ALF-205-01	1	0.98	3.53	2.36	4.33	1.13



*LEAD FREE: The wetted surfaces of this product shall contain no more than 0.25% lead by weighted average. Complies with Federal Public Law 111-380. ANSI 3rd party approved and listed.