
wolfappliance.com

## **FEATURES**

- Three-speed blower control with boost.
- Remote-mounted control module with LED indicators.
- Delay-off feature to automatically turn unit off.
- Stainless steel, mesh filters.
- Reversible motor box.
- Adjustable discharge.





BLOWER OPTIONS*	
MODEL DD45	CFM
Internal	600
In-line	600

In-line 600 Remote 600 or 1200

\*Blowers sold separately.

IMPORTANT NOTE: Wolf downdrafts can be used with all Wolf induction, electric and gas cooktops, except unframed models. Wolf downdrafts cannot be used with the steamer or fryer module and are not recommended for use with the electric grill module.

## **ACCESSORIES**

- Make-up air damper.
- 8" Inline damper.
- 10" Inline damper.

Accessories available through an authorized Wolf dealer. For local dealer information, visit the find a showroom section of our website, wolfappliance.com.




wolfappliance.com

SPECIFICATIONS	
PRODUCT Dimensions Weight	45"W x 14"H x 2"D 85 lb
DISCHARGE Internal In-line or Remote	6" Round 10" Round
Supply Service Power Cord	120 VAC, 60 Hz 15 amp circuit 4 ft

Specifications are subject to change without notice. Visit wolfappliance.com/specs for the most up-to-date information.


Dimensions may vary  $\pm ^{1}/\epsilon "$  (3). Dimensions in parentheses are millimeters unless otherwise specified.


## **DIMENSIONS**




NOTE: Shaded line represents internal blower box with 6" (152) round discharge.

## **INSTALLATION WITH COOKTOP**







 $^*6$ " (152) back from the countertop cutout when an internal blower is rear mounted.

NOTE: Internal blower 6" (152) round, side, rear or bottom discharge. In-line and remote blower 10" (254) round, rear discharge. Centerline indicates center of downdraft cut-out.

©Wolf Appliance, Inc. all rights reserved.