


TOWN SQUARE® PRESSURE BALANCE BATH/SHOWER FITTING

WITH FloWise® SHOWERHEAD



T555.528 Bath/Shower Trim Shown with M962055 Decorative Screw Cover Plate

GENERAL DESCRIPTION:

SHOWERHEAD

FloWise water saving 3-function showerhead offers up to 40% water savings at maximum 2.0 gpm/7.6 L/min. flow rate.

WALL TUB SPOUT

Metal slip-on diverter spout.

WALL VALVE TRIM


Available with metal lever handle. Metal wall escutcheon.

MODEL NUMBER:

TRIM KITS:

- T555.528 Town Square BATH/SHOWER Trim Kit Metal Lever Handle. FloWise® Showerhead. LESS Valve Body.
- T555.527 Town Square SHOWER ONLY Trim Kit Metal Lever Handle. FloWise® Showerhead. LESS Valve Body.
- ADDITIONAL ACCESSORIES: M962055 Decorative Screw Cover Plate

For use with R120 Series Pressure Balance Valves. See reverse side for available Rough Valves.



SUGGESTED SPECIFICATION:

Bath/shower fitting shall feature water saving 3-function showerhead with Max. 2.0 gpm/7.6 L/min. flow rate. Fitting shall be: American Standard - Trim Kit Model # T555.52_.___ and Valve Body Model # R12_.




TOWN SQUARE® PRESSURE BALANCE BATH/SHOWER FITTING WITH FloWise® SHOWERHEAD


CODES AND STANDARDS

These products meet or exceed the following codes and standards:

ANSI A 117.1 **ASSE 1016** ASME A112.18.1 CSA B 125.1



*To modify a product, add suffix after the 4th digit (ex. T064<u>ITP</u>502.002)



		* TRIM & ROUGH MUST BE ORDERED SEPARATELY.	Finish Options		
TRIM KITS *	Product		Polished Chrome	Oil Rubbed Bronze	PVD Satin Nickel
	Number	Description	002	224	295
	T555.528	Bath/Shower Trim Kit. Metal Lever Handle. FloWise Showerhead. LESS Valve Body.			
	T555.527	Shower Only Trim Kit. Metal Lever Handle. FloWise Showerhead. LESS Valve Body.			
	M962055	Decorative Screw Cover Plate			

	Product Number	Description
ROUGH VALVE BODIES	R121	Rough Valve Body less trim. Universal inlets/outlets.
	R121SS	Rough Valve Body less trim. Universal inlets/outlets with Screwdriver Stops.
	R120	Rough Valve Body less trim. Direct Sweat inlets/outlets.
	R120SS	Rough Valve Body less trim. Direct Sweat inlets/outlets with Screwdriver Stops.
	R125	Rough Valve Body less trim. Female Thread inlets/outlets.
	R125SS	Rough Valve Body less trim. Female Thread inlets/outletswith Screwdriver Stops.
	R127	Rough Valve Body less trim. PEX inlets/universal outlets for Crimp Ring PEX system (ASTM F1807).
	R127SS	Rough Valve Body less trim. PEX inlets/universal outlets for Crimp Ring PEX system (ASTM F1807) with Screwdriver Stops.
	R128	Rough Valve Body less trim. PEX inlets/universal outlets for Cold Expansion PEX system (ASTM F1960).
	R128SS	Rough Valve Body less trim. PEX inlets/universal outlets for Cold Expansion PEX system (ASTM F1960) with Screwdriver Stops.
	R129	Rough Valve Body less trim. CPVC inlets/universal outlets.
	R129SS	Rough Valve Body less trim. CPVC inlets/universal outlets with Screwdriver Stops.

Meets the American Disabilities Act Guidelines and ANSI A117.1 £

Requirements for the physically challenged.